

PUSHRODS & GLORODS

Product Features:

Where are they used?

For security alarm, home theater and CATV and Satellite installation. Install wires above the ceiling, in insulated walls, under the carpet and raised floors, and more.

What is a PushRod/GloRod?

Non-conductive Fiberglass Rods for wiring. These non-conductive rods are perfect for drop ceilings, attics, floors, walls, and crawl spaces. Their high strength and flexibility handle turns easily without breaking. Designed for maximum versatility, threaded ferrules make it possible to customize rod length to any job, making it easier to handle any wiring. GloRods provide a handy glow-in-the-dark feature for added convenience in dark spaces.



Features

PUSHROD PR-12

- 1/4" Diameter
- Used for long spans
- Minimum bend radius: 6"
- Tensile/Pull Strength: 750lbs
- Contains 5 easy to connect fiberglass rods: 3 1/4" x 6', 1 1/4" x 3', and 1 3/16" x 3'

PUSHROD PR-24

- 1/4" Diameter
- Used for long spans
- Minimum bend radius: 6"
- Tensile/Pull Strength: 750lbs
- Contains 3 easy-to- connect fiberglass rods: 1/4" x 4'

GLOROD GR-15

- 3/16" Diameter
- More flexible for short runs or use in limited space
- Minimum bend radius: 4"
- Tensile/Pull Strength: 500lbs
- contains 5 easy-to- connect fiberglass rods: 3/16" x 5'
- Glows in the dark

GLOROD GR-18

- 5/32" Diameter
- smallest diameter offers extreme flexibility with high strength
- Minimum bend radius: 3.5"
- Tensile/Pull Strength: 300lbs
- contains 3 easy-to- connect fiberglass rods: 5/32" x 6'
- Glows in the dark

SPECIFICATIONS:

	PUSHROD LONG	PUSHROD SHORT	GLOROD KIT	GLOROD KIT 18'
Overall Length	24' (7.3m)	12' (3.6m)	15' (4.6m)	18' (5.5m)
Tensile Pull/ strength	750 lbs	750 lbs	500 lbs	300 lbs
Length	Contains 5 easy to connect fiberglass rods: 3¼" x 6" (6mm x 1.2mm), 1¼" x 3' (6mm x .9mm) and 1¾" x 3' (5mm x .9mm)	Contains 3 easy to connect fiberglass rods: ¼" x 4' (6mm x 1.2mm)	Contains 3 easy to connect fiberglass rods: 3/16" x 5' (5mm x 1.5mm)	Contains 3 easy to connect fiberglass rods: 5/32" x 6' (4mm x 1.8mm)
Diameter	¼" (6.4mm)	¼" (6.4mm)	3/16" (4.7mm)	5/32" (4.0mm)
Weight	1.04 lbs (0.5kg)	1.04 lbs (0.5kg)	1 lbs (0.5kg)	.8 lbs (0.4 kg)
Minimum Bend Radius	6½" (165mm)	6½" (165mm)	4¼" (108mm)	3½" (89mm)

ORDERING INFORMATION:

CAT. NO.	DESCRIPTION
PR-24	PUSHROD, Long (24)
GR-15	GLO ROD KIT
PR-12	PUSHROD, SHORT (12)
GR-18	GLO ROD KIT, 18'



1390 Aspen Way Vista, CA • 92081

TC-PRGR 11/2020

Latin America Phone : 1.760.510.0558 | EMEA Phone: +44 (0) 1633 927 050

©2020 Tempo Inc. • An ISO 9001 Company

EMEA Address: Tempo Europe Limited • Brecon House

William Brown Close • Cwmbran • NP44 3AB • UK

TempoCom.com | tel 800.642.2155 | sales@tempocom.com



Renewed Vision. Innovation Forward.



Follow Us
[@TempoComms](https://www.instagram.com/tempocomms)