






Compact All-In-One NVR Appliance

The CR67 compact video server (NVR) has been designed for performance and peace of mind. Offering recording capacity up to 20TB, the CR67 offers key features such as pre-installed operating system, high performance INTEL processor, dedicated SSD boot drive (OS), dual SATA drives and Gigabit Ethernet.

Features

- Low Noise Compact Design
- Intel® Core i7 Series Processor
- Dual-Purpose Recording & Live Viewing
- Dedicated SSD Boot Drive
- Up to 20TB Internal Video Storage
- Designed for 24/7 Video Recording
- Dual SATA drive configurations available
- Pre-Loaded Windows 10 Enterprise
- Ready for any VMS deployment





3 Year Waranty



Made for IP Video



Full Turnkey System



Multi-Display Support

Built to last

High performance solid state boot drive, internal realtime hardware and software watchdogs and fully recoverable operating system image extends the reliability of your critical installations.

Recommended VMS platforms













CR67 Specifications

Compact All-In-One NVR Appliance

System

Processor Intel® Core i7-9700 (passmark: 15951)

12M Cache, up to 4.70 GHz

Memory 8GB DDR4

Network 2 x 10/100/1000 Base-T Ethernet port(s) RJ45

USB 4 x USB 3.0

2 x USB 2.0

Video Outputs Intel® UHD Graphics 630

Multi output support : HDMI/DVI-D/VGA

- HDMI 1.4b max. 4096x2160@24Hz / 25600x1600@60Hz

- DVI-D with max. 1920x1200@60Hz - VGA with max. 1920x1200@60Hz

Audio 8-Channel High Definition Audio

Boot Drive Min. 240GB Solid State Boot Drive (SSD)

Video Storage 2 x 3.5" SATA A/V HDD (up to 20TB)

Operating System Windows 10 Enterprise

Recommended VMS Avigilon, Axis, Exacq, Genetec, Milestone

Protocols

Networking IPv4, UDP, TCP, IGMP, ARP, DHCP,

DNS, HTTP, HTTPS, BONJOUR, NTP

Management HTTP, HTTPS, Bonjour, ION API, SNMP

Security Basic / Digest Authentication, SSL

Software Features

Web Interface Web GUI for remote config. / maintenance

Programming API Bonjour discovery protocol

ION API for configuration

Firmware Update Fault-tolerant, remote accessible

Mechanical / Environmental

Dimensions 12.20" (W) x 3.94" (H) x 10.43" (D)

Power Supply Internal Standard TFX 12V, 200W

(US Power Cord Included)

Security Padlock Loop / Kensington Slot

Operating Temp. 0°C - 40°C

Warranty 3 Years Standard

Compliance RoHS, CE and FCC Class B

NODES

www.ionodes.com

Head Office 1855 Bernard-Lefebvre,

Laval, Quebec H7C 0A5, Canada

sales@ionodes.com

1.450.696.1060 1.844.696.1060 (Toll Free) EMEA Office

15, Rue de l'Industrie, Bertrange, L-8069 Luxembourg

sales_eu@ionodes.com

+33 (0) 6 03 13 79 75

Ordering Information

 $\begin{array}{lll} \text{CR67-04-04TB} & \text{CR67 with 1 x 4TB of internal storage.} \\ \text{CR67-08-08TB} & \text{CR67 with 1 x 8TB of internal storage.} \\ \text{CR67-10-10TB} & \text{CR67 with 1 x 10TB of internal storage.} \\ \text{CR67-04-08TB} & \text{CR67 with 2 x 4TB of internal storage.} \\ \text{CR67-08-16TB} & \text{CR67 with 2 x 8TB of internal storage.} \\ \text{CR67-10-20TB} & \text{CR67 with 2 x 10TB of internal storage.} \\ \end{array}$

CR67-PWR-EUUK CR67-RM CR67 power cord kit for EU and UK regions. 2U vented universal depth shelf for

server racks.