

## Heavy-Duty USB-A to USB-C Cable, USB 2.0, UHMWPE and Aramid Fibers, (M/M), Gray, 10 ft. (3.05 m)

MODEL NUMBER: **U038-010-GY-MAX**



Durable USB cable connects a smartphone or other USB-C device to the USB-A port on your computer, wall charger or car charger.

### Features

**Heavily Reinforced USB 2.0 Cable Charges and Syncs Your Phone or Other USB-C Device** This heavy-duty USB sync/charge cable (M/M) connects your smartphone, tablet, MacBook, Ultrabook, Chromebook or other USB-C device to the USB-A port on a computer, car charger or wall charger. It allows you to charge and power your USB-C device, while simultaneously syncing and transferring data at USB 2.0 data transfer speeds up to 480 Mbps. The cable is backward compatible with previous USB generations, allowing you to use it with older equipment.

**Constructed Using UHMWPE and Bulletproof Aramid Fiber Designed to Last** Charging cables used with mobile devices are often pulled, strained and generally abused, sometimes to the point of failure. To counter the stress of daily abuse, the super-robust U038-010-GY-MAX is constructed using UHMWPE and Aramid fiber to reinforce the conductors inside the cable. The double-braided nylon jacket helps maintain top performance and long life, while the enhanced UHMWPE and Aramid protection stands up to the strain of rigorous and frequent use. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable move freely without cracking or breaking loose from the connector.

**Reversible USB-C Connector Attaches in Either Direction** Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for a fumble-free connection every time. The cord's 10-ft. (3.05 m) length allows you flexibility in placing your device with respect to the connected computer or charger.

### Highlights

- Engineered using UHMWPE and Aramid fiber to stand up to frequent and rigorous use
- Extra-strong cable construction helps prevent fraying and loose cable connectors
- Supports USB 2.0 speeds up to 480 Mbps to ensure efficient charging and data transfers
- Integral strain relief helps cable move freely without stress or cracking
- Reversible USB-C plug connects in either direction for immediate no-fuss use

### Applications

- Charge and sync your MacBook, Chromebook or other USB-C device from a USB computer or wall charger up to 10-ft. (3.05 m) away
- Transfer data between an external hard drive and your USB-C notebook or computer
- Replace a cable that became frayed or inoperable due to frequent use

### System Requirements

- Device or charger with USB-A port
- Device with USB-C port

### Package Includes

- U038-010-GY-MAX Heavy-Duty USB-A to USB-C Cable (M/M), Gray, 10-ft. (3.05 m)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

## Specifications

OVERVIEW	
UPC Code	037332241344
Technology	USB 2.0 (High Speed); USB
PHYSICAL	
Color	Gray
Cable Outer Diameter (OD)	4.2 mm
Cable Jacket Rating	VW-1
Cable Length (ft.)	10
Cable Length (m)	3
Cable Length (in.)	120
Material of Construction	PVC, UHMWPE, Aramid
Cable Length (cm)	304.8
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 10.00
Shipping Weight (kg)	0.10
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	-4 to 140 F (-20 to 60 C)
Storage Temperature Range	-4 to 176 F (-20 to 80 C)
Relative Humidity	0% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB C (MALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
STANDARDS & COMPLIANCE	
Certifications	Tested to CE, RoHS, REACH



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>