

Dual-Port USB Car Charger with 30W Charging - USB-C (18W) QC 3.0, USB-A (12W), Coiled 6 ft. (1.83 m) USB-C Cable, Black

MODEL NUMBER: **U280-C02-30W-C6**



2-port car charger with built-in coiled USB-C cable charges 2 tablets, smartphones and other USB-C or USB-A devices at the same time.

Features

USB Car Charger Safely Charges 2 Mobile Devices in Your Vehicle Simultaneously This dual-port USB car charger with Quick Charge (QC) 3.0 technology lets you quickly and safely charge two USB mobile devices at the same time. You and a passenger can connect your smartphones, tablets, notebooks or power banks, to name just a few compatible devices, to ensure satisfactory battery charge when you reach your destination.

Charges QC 3.0-Compatible Devices up to 4 Times Faster than Standard Chargers Instead of charging at a preset power level, the 18W USB-C cable adjusts to the appropriate power level (3.6–6V 3A, 6–9V 2A or 9–12V 1.5A) to provide as much charge as your QC-compliant device's battery can handle. The specially coiled cable takes up much less space in your vehicle than a regular 6-ft. (1.83 m) cable. It also resists tangles and knots to avoid cable clutter on the road.

Built-In Auto-Sensing Adjusts to Proper Power Level to Get Your Device to 100% The USB-A port features auto-sensing technology that detects the connected device and automatically adjusts to the appropriate power level up to 5V/2.4A, perfect for fast-charging tablets and e-readers. The U280-C02-30W-C6 protects against overheating, overcurrent and overcharging. In fact, it stops charging as soon as your devices' batteries are at full capacity.

Plugs into the 12V DC Power Outlet in Your Vehicle The compact charger connects to any standard 12V DC vehicle power outlet, such as the one on your dashboard. Just plug it in and connect it to your devices for fast, convenient mobile charging. An easy-to-see blue LED indicates the charger is receiving power. The U280-C02-30W-C6 is compatible with Apple (including iPhone), Android (including Samsung), Windows and Amazon devices with USB-A, USB-C or Thunderbolt 3 charging ports.

Highlights

- 2-port USB charger connects to the 12V DC power outlet in your car, truck or SUV
- Ideal for charging smartphones, tablets, e-readers and notebooks while traveling
- Maximum charging power output of 30W: 18W USB-C and 12W USB-A
- Built-in 6-ft. (1.83 m) USB-C cable is coiled to take up less space in your vehicle
- USB-C Quick Charge 3.0 cable charges up to 4x faster than conventional USB chargers

Applications

Charge up to 2 smartphones, tablets, power banks, e-readers, notebooks or any other USB-A, USB-C or Thunderbolt 3 devices while driving to your destination

System Requirements

Vehicle with standard 12V DC power outlet

Package Includes

U280-C02-30W-C6 Dual-Port USB Car Charger, Coiled USB-C Cable, Black

Specifications

OVERVIEW	
UPC Code	037332256508
Over Current Protection	Yes
Technology	USB



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

INPUT	
Input Connection Type	Car Auxiliary Power Outlet
Built-In Cable Length (ft.)	6
Built-In Cable Length (m)	1.828
Built-In Cable Length (in.)	72
Built-In Cable Length (cm)	182.88
OUTPUT	
Output Capacity	USB-C: 3.6-6V/3A, 6-9V/2A, 9-12V/1.5A; USB-A: 5V/2.4A
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue - Power
CHARGING	
Number of Charging Ports	2
Total Charging Watts	30
Charging Method	USB
Charging Ports / Amps	(1) 2.4A; (1) 3A / 2A / 1.5A
PHYSICAL	
Color	Black
Material of Construction	Polycarbonate, ABS
Unit Dimensions (hwd / cm)	7.05 x 2.56 x 3.76
Unit Dimensions (hwd / in.)	2.775 x 1.007 x 1.48
Unit Packaging Type	Polybag
Unit Weight (kg)	0.06
Unit Weight (lbs.)	0.132
ENVIRONMENTAL	
Operating Temperature Range	32 to 77 °F (0 to 25 °C)
Storage Temperature Range	-4 to 140 °F (-20 to 60 °C)
Operating Humidity Range	30 to 90% RH, NON-CONDENSING
Storage Humidity Range	10 to 90% RH, NON-CONDENSING
CONNECTIONS	
Ports	1
Side A - Connector 1	Car Cigarette Lighter



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Side B - Connector 1	USB A (FEMALE)
Side B - Connector 2	USB C (MALE)
FEATURES & SPECIFICATIONS	
Driver Required	No
Quick Charge Compliant	3.0
STANDARDS & COMPLIANCE	
Certifications	ROHS, REACH, CE, FCC, WEEE
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>