



## KVM Cables & Dongles




### Single Console Cable

	
<b>CB-6A</b> VGA Console Cable (6ft/1.8M)	<b>CX-6A</b> DVI-D Console Cable (6ft/1.8M)
Resolution Support	
16:10	max. 1920 x 1200
16:9	max. 1920 x 1080
4:3	max. 1600 x 1200




Cables and Dongles for use with CyberView range of LCD Console Drawers and KVM Switches



### DB-15 VGA USB Cable

		
<b>CB-6</b> DB-15 Cable (6ft/1.8M)	<b>CB-10</b> DB-15 Cable (10ft/3M)	<b>CB-15</b> DB-15 Cable (15ft/4.5M)
Resolution Support		
16:10		max. 1920 x 1200
16:9		max. 1920 x 1080
4:3		max. 1600 x 1200



### DVI-D USB Cable

	
<b>CI-6</b> DVI-D Cable (6ft/1.8M)	<b>CI-15</b> DVI-D Cable (15ft/4.5M)
Resolution Support	
16:10	max. 1920 x 1200
16:9	max. 1920 x 1080
4:3	max. 1600 x 1200






### 4K KVM Cable

	
<b>CK-6P</b> DP KVM Cable (6ft/1.8M)	<b>CK-6H</b> HDMI KVM Cable (6ft/1.8M)
Resolution Support	
16:10	max. 1920 x 1200
16:9	max. 3840 x 2160
4:3	max. 1600 x 1200

### 2K KVM Cable

	
<b>CH-6D</b> DVI-D Console Cable (6ft/1.8M)	<b>CH-6H</b> HDMI Console Cable (6ft/1.8M)
Resolution Support	
16:10	max. 1920 x 1200
16:9	max. 2560 x 1440
4:3	max. 1600 x 1200

### Cat6 KVM Dongle

				
<b>DG 100P</b> DP-USB Dongle	<b>DG-100H</b> HDMI-USB Dongle	<b>DG-100SD</b> DVI-USB Dongle	<b>DG-100S</b> VGA-USB Dongle	<b>DG-100</b> VGA-PS/2 Dongle
Resolution Support				
	16:10			max. 1920 x 1200
	16:9			max. 1920 x 1080
	4:3			max. 1600 x 1200

\*Resolution Support relates to LCD specification