

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2210509000

Status:

Active

Overview:

mPm DIN Valve Connectors

Description:

mPm DIN Valve Connector, Form C - Micro 9.4mm, 2 Pole, to 3.0m WSOR UL Cable Pigtail, Yellow LED + VDR, Black Profile NBR Gasket, 24V

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Industrial Cordsets

Series

221050

Connector End A

Brad mPm DIN C - Micro 9.4mm

Connector End B

Pigtail

IP Rating

IP65

Material - Contact

Brass

Overview

mPm DIN Valve Connectors

Product Name

mPm

Protocol

EtherNet

Region

America, Europe

Type

Single Ended

UPC

889056669269

Physical

Cable Diameter

5.60mm (.220")

Cable Length

3.0m (9.84')

Color - Cable Jacket

Black

Coupling Style

Threaded

Gender

Male-Pigtail

Keyway

None

LED Indicator

Yellow

Material - Cable Jacket

WSOR UL

Material - Connector Body

Polypropylene

Material - Coupling Nut

N/A

Material - Plating Mating

N/A

Net Weight

344.000/g

Orientation

90° to Pigtail

Poles

2

Temperature Range - Operating

-40°C to +90°C

Wire Size AWG

20

Wire/Cable Type

N/A

Electrical

Current - Maximum per Contact

N/A

Voltage - Maximum

24V

Material Info

Engineering Number

E392W2A30011C4H

Reference - Drawing Numbers

Sales Drawing

SD-121050-007-001



Series image - Reference only

EU ELV

Not Compliant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)9139-DC (19 Jan 2021)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Not Relevant

Not Compliant

Not Contained

Search Parts in this Series

221050 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION