

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1212100342

Status:

Active

Overview:

Description:

mPm DIN Valve Connector, Form C-8mm, External Threads, 2 Pole Plus Ground with C4 Circuit, 24V, Yellow LED + VDR, Transparent, Profiled NBR Gasket, Bulk Pack, Mounted

General	
Product Family	Field Attachable / Accessories
Series	121210
Form	C - 8mm
IP Rating	IP67
Material - Contact	Brass
Overview	mpm_connectors
Product Name	mPm
Type	Field Attachable Connector
UPC	884982541856
Physical	
Cable Diameter	3.00-5.50mm
Coupling Type	External Thread
Diagnostics / LEDs	Yes
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	Polyamide
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Net Weight	896.000/g
Orientation	90° Angle
Pitch - Mating Interface	8.00mm
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	16.0A
Voltage - Maximum	24V
Material Info	
Engineering Number	S25200TC4H2TSN
Reference - Drawing Numbers	
Packaging Specification	PK-121210-S25-001
Sales Drawing	SD-121210-001
Test Summary	STR-1299-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

121210 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION