

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1212110032

Status:

Active

Overview:

mPm DIN Valve Connectors

Description:

mPm DIN Valve Connector, Form C - Micro 9.4mm, External Threads, 2 Pole Plus Ground with C4 Circuit, 24V, Yellow LED + VDR, Transparent, Profiled NBR Gasket, Single Bag, Unmounted



Documents:

Drawing (PDF)

Product Specification PS-121201-001-001 (PDF)

Product Specification STR-1251-001 (PDF)

Packaging Specification PK-121211-S29-001 (PDF)

Test Summary STR-1299-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Field Attachable / Accessories
Series	121211
Form	C - Micro 9.4mm
IP Rating	IP67
Material - Contact	Brass
Overview	mPm DIN Valve Connectors
Product Name	mPm
Type	Field Attachable Connector
UPC	884982530843
Physical	
Cable Diameter	3.00-5.50mm
Coupling Type	External Thread
Diagnostics / LEDs	Yes
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	Polyamide
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Net Weight	15.103/g
Orientation	90° Angle
Pitch - Mating Interface	9.40mm
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	16.0A
Voltage - Maximum	24V
Material Info	
Engineering Number	S29200TC420T
Reference - Drawing Numbers	
Packaging Specification	PK-121211-S29-001
Product Specification	PS-121201-001-001, STR-1251-001
Sales Drawing	SD-121211-001
Test Summary	STR-1299-001

EU ELV

Not Reviewed

EU RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit

Contact US

China ROHS

ELV

RoHS Phthalates

Not Relevant

Not Reviewed

Not Contained

Search Parts in this Series

121211 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION