

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2210509010

Status:

Active

Overview:

mPm DIN Valve Connectors

Description:

mPm DIN Valve Connector, Form C - 8mm, 2 Pole, to 3.0m WSOR UL Cable Pigtail, Yellow LED + VDR, Black Profile NBR Gasket, 24V

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Cordsets
Series	221050
Connector End A	Brad mPm DIN C - 8mm
Connector End B	Pigtail
IP Rating	IP65
Material - Contact	Brass
Overview	mPm DIN Valve Connectors
Product Name	mPm
Protocol	EtherNet
Region	America, Europe
Type	Single Ended
UPC	889056669368
Physical	
Cable Diameter	5.60mm (.220")
Cable Length	3.0m (9.84')
Color - Cable Jacket	Black
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	None
LED Indicator	Yellow
Material - Cable Jacket	WSOR UL
Material - Connector Body	Polypropylene
Material - Coupling Nut	N/A
Material - Plating Mating	N/A
Net Weight	366.000/g
Orientation	90° to Pigtail
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size AWG	20
Wire/Cable Type	N/A
Electrical	
Current - Maximum per Contact	N/A
Voltage - Maximum	24V
Material Info	
Engineering Number	E492W2A30011C4H
Reference - Drawing Numbers	
Sales Drawing	SD-121050-002-001



Series image - Reference only

EU ELV	
Not Compliant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

221050 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION