

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300478008](#)
Status: **Active**
Overview:
Description: Brad RJ-45 Field Attachable Connector, 8 Poles, Straight, Male, Shielded, IDC Termination, AWG 24-22

Agency Certification

UL E361772

General

Product Family Field Attachable / Accessories
Series [130047](#)
Approvals UL Listed: E244889, cCSAus certified
Comments POE+ according to IEEE 802.3AT
Communication Speed 10-Gigabit Ethernet
IP Rating IP20
Material - Contact Brass
Overview brad_industrial_ethernet_solutions
Product Name RJ45 Cat6A
Type Field Attachable Connector
UPC 889056622509

Physical

Cable Diameter 5.00-9.00mm (.197-.354")
Coupling Type Push to Lock
Diagnostics / LEDs No
Diagnostics Port No
Gender Male
Keyway X-coded
Material - Connector Body Zinc Die-Cast with Nickel
Material - Coupling Nut Clear UL 94 V0
Material - Plating Mating Gold
Net Weight 20.860/g
Orientation Straight
Poles 8
Temperature Range - Operating -40°C to +85°C
Wire Size AWG 24-22/1

Electrical

Current - Maximum per Contact 0.5A
Voltage - Maximum 48V

Material Info

Engineering Number E6AS06-5

Reference - Drawing Numbers

Sales Drawing 1300478008-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[130047](#) Series