

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1210401279

Status:

Active

Overview:

mPm DIN Valve Connectors

Description:

mPm DIN Valve Connector, Form A - 18mm, 2 Pole, to 1.0m PUR UL Cable Pigtail, Black Integrated Gasket



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Cordsets
Series	121040
Connector End A	Brad mPm DIN A - 18mm
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Brass
Overview	mPm DIN Valve Connectors
Product Name	mPm
Protocol	EtherNet
Region	America, Europe
Type	Single Ended
UPC	78172554433
Physical	
Cable Diameter	6.50mm (.256")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Black
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	None
LED Indicator	No
Material - Cable Jacket	PUR UL
Material - Connector Body	Polypropylene
Material - Coupling Nut	N/A
Material - Plating Mating	N/A
Net Weight	425.000/g
Orientation	90° to Pigtail
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size AWG	18
Wire/Cable Type	N/A
Electrical	
Current - Maximum per Contact	N/A
Voltage - Maximum	N/A
Material Info	
Engineering Number	E152B3A1001P
Reference - Drawing Numbers	
Sales Drawing	1210400050-000

EU ELV Compliant	
EU RoHS Compliant	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

121040 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION