

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1210503140

Status:

Active

Overview:

mPm DIN Valve Connectors

Description:

mPm DIN Valve Connector, Form A - 18mm, 2 Pole, to 3.0m PUR UL Cable Pigtail, Yellow LED + Transil, Black Integrated Gasket, 24V

Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family

Industrial Cordsets

Series

121050

Connector End A

Brad mPm DIN A - 18mm

Connector End B

Pigtail

IP Rating

IP67

Material - Contact

Brass

Overview

mPm DIN Valve Connectors

Product Name

mPm

Protocol

EtherNet

Region

America, Europe

Type

Single Ended

UPC

78172511980

Physical

Cable Diameter

6.50mm (.256")

Cable Length

3.0m (9.84')

Color - Cable Jacket

Black

Coupling Style

Threaded

Gender

Male-Pigtail

Keyway

None

LED Indicator

Yellow

Material - Cable Jacket

PUR UL

Material - Connector Body

Polypropylene

Material - Coupling Nut

N/A

Material - Plating Mating

N/A

Net Weight

333.000/g

Orientation

90° to Pigtail

Poles

2

Temperature Range - Operating

-40°C to +90°C

Wire Size AWG

18

Wire/Cable Type

N/A

Electrical

Current - Maximum per Contact

N/A

Voltage - Maximum

24V

Material Info

Engineering Number

E452B3A3001PS0H

Reference - Drawing Numbers

Sales Drawing

1210502000-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 7(c)-I

REACH SVHC

Contained Per - ED/01/2017 (12 January 2017)

2,4-di-tert-butyl-6-(5-chlorobenzotriazol-2-yl)p

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

121050 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION