

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2210400001

Status:

Active

Overview:

Description:

mPm DIN Valve Connector, Form B - 11mm, 2 Pole, to 3.0m WSOR UL Cable Pigtail, Black Profile NBR Gasket

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)9139-DC (19 Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Relevant

Agency Certification	
UL	E218123
General	
Product Family	Industrial Cordsets
Series	221040
Connector End A	Brad mPm DIN B - 11mm
Connector End B	Pigtail
IP Rating	IP65
Material - Contact	Brass
Overview	mpm_connectors
Product Name	mPm
Protocol	EtherNet
Region	America, Europe
Type	Single Ended
UPC	889056668095
Physical	
Cable Diameter	6.40mm (.252")
Cable Length	3.0m (9.84')
Color - Cable Jacket	Black
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	None
LED Indicator	No
Material - Cable Jacket	WSOR UL
Material - Connector Body	Polypropylene
Material - Coupling Nut	N/A
Material - Plating Mating	N/A
Net Weight	344.000/g
Orientation	90° to Pigtail
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size AWG	18
Wire/Cable Type	N/A
Electrical	
Current - Maximum per Contact	N/A
Voltage - Maximum	N/A
Material Info	
Engineering Number	E162W3A30021
Reference - Drawing Numbers	
Sales Drawing	1210400254-000

Search Parts in this Series

221040 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION