

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2210400006

Status:

Active

Overview:

mPm DIN Valve Connectors

Description:

mPm DIN Valve Connector, Form C - 8mm, 2 Pole, to 3.0m WSOR UL Cable Pigtail, Black Profile NBR Gasket



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E218123
General	
Product Family	Industrial Cordsets
Series	221040
Connector End A	Brad mPm DIN C - 8mm
Connector End B	Pigtail
IP Rating	IP65
Material - Contact	Brass
Overview	mPm DIN Valve Connectors
Product Name	mPm
Protocol	EtherNet
Region	America, Europe
Type	Single Ended
UPC	889056669245
Physical	
Cable Diameter	5.60mm (.220")
Cable Length	3.0m (9.84')
Color - Cable Jacket	Black
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	None
LED Indicator	No
Material - Cable Jacket	WSOR UL
Material - Connector Body	Polypropylene
Material - Coupling Nut	N/A
Material - Plating Mating	N/A
Net Weight	355.000/g
Orientation	90° to Pigtail
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size AWG	20
Wire/Cable Type	N/A
Electrical	
Current - Maximum per Contact	N/A
Voltage - Maximum	N/A
Material Info	
Engineering Number	E432W2A30011

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)4578-DC (25 June 2020)	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Reviewed
RoHS Phthalates	Not Contained

Search Parts in this Series

221040 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION