

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1212010044](#)
Status: **Active**
Overview: mPm DIN Valve Connectors
Description: mPm DIN Valve Connector, Form A-18mm, External Thread, 2 Pole Plus Ground Terminal, 250V AC/DC, Black, Integrated NBR Gasket, UL94-V0 Rated, Bulk Pack, Mounted

Documents:
[Drawing \(PDF\)](#) [Packaging Specification PK-121201-C28-001 \(PDF\)](#)
[Product Specification PS-121201-001-001 \(PDF\)](#) [Test Summary TS-121201-001-001 \(PDF\)](#)
[Product Specification STR-1251-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification		
UL		E218123
General		
Product Family		Field Attachable / Accessories
Series		121201
Form		A - 18mm
IP Rating		IP67
Material - Contact		Brass
Overview		mPm DIN Valve Connectors
Product Name		mPm
Type		Field Attachable Connector
UPC		887191043777

Physical		
Cable Diameter		4.00-9.00mm
Coupling Type		External Thread
Diagnostics / LEDs		No
Diagnostics Port		No
Gender		N/A
Keyway		None
Material - Connector Body		Polyamide
Material - Coupling Nut		N/A
Material - Plating Mating		Silver
Net Weight		21.550/g
Orientation		90° Angle
Pitch - Mating Interface		18.00mm
Poles		2
Temperature Range - Operating		-40°C to +90°C
Wire Size AWG		N/A

Electrical		
Current - Maximum per Contact		16.0A
Voltage - Maximum		250V AC/DC

Material Info		
Engineering Number		C28200W2RSNSA

Reference - Drawing Numbers		
Packaging Specification		PK-121201-C28-001
Product Specification		PS-121201-001-001, STR-1251-001
Sales Drawing		SD-121201-003-001
Test Summary		TS-121201-001-001



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant with Exemption 6(c) REACH SVHC Contained Per - D(2020)9139-DC (19 Jan 2021) Lead Halogen-Free Status Low-Halogen For more information, please visit Contact US	China RoHS 50 Image Not Relevant Not Contained

Search Parts in this Series
[121201](#) Series

This document was generated on 06/14/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION