

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1212010046

Status:

Active

Overview:

mPm DIN Valve Connectors

Description:

mPm DIN Valve Connector, Form A-18mm, External Thread, 3 Pole Plus Ground Terminal, 250V AC/DC, Black, Integrated NBR Gasket, UL94-V0 Rated, Bulk Pack, Mounted



Documents:

Drawing (PDF)

Product Specification PS-121201-001-001 (PDF)

Product Specification STR-1251-001 (PDF)

Packaging Specification PK-121201-C28-001 (PDF)

Test Summary TS-121201-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Field Attachable / Accessories
Series	121201
Form	A - 18mm
IP Rating	IP67
Material - Contact	Brass
Overview	mPm DIN Valve Connectors
Product Name	mPm
Type	Field Attachable Connector
UPC	887191089539
Physical	
Cable Diameter	4.00-9.00mm
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	Polyamide
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Net Weight	23.074/g
Orientation	90° Angle
Pitch - Mating Interface	18.00mm
Poles	3
Temperature Range - Operating	-40°C to +90°C
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	16.0A
Voltage - Maximum	250V AC/DC
Material Info	
Engineering Number	C28300W2RSNSA
Reference - Drawing Numbers	
Packaging Specification	PK-121201-C28-001
Product Specification	PS-121201-001-001, STR-1251-001
Sales Drawing	SD-121201-003-001
Test Summary	TS-121201-001-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Relevant	
REACH SVHC	
Not Relevant	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Relevant

Search Parts in this Series

121201 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION