

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1212040010](#)
Status: **Active**
Overview: [mPm DIN Valve Connectors](#)
Description: mPm DIN Valve Connector, Form C-8mm, External Thread, 2 Pole Plus Ground Terminal, 250V AC/300V DC, Black, Nitrile Gasket, Bulk Pack, Mounted

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-121204-C25-001 \(PDF\)](#)
[Product Specification PS-121201-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Field Attachable / Accessories
Series [121204](#)
Form C - 8mm
IP Rating IP65, IP67
Material - Contact Brass
Overview [mPm DIN Valve Connectors](#)
Product Name mPm
Type Field Attachable Connector
UPC 884982586666

Physical

Cable Diameter N/A
Coupling Type External Thread
Diagnostics / LEDs No
Diagnostics Port No
Gender N/A
Keyway None
Material - Connector Body Polyamide
Material - Coupling Nut N/A
Material - Plating Mating Silver
Net Weight 23.133/g
Orientation 90° Angle
Pitch - Mating Interface 8.00mm
Poles 2
Temperature Range - Operating -40°C to +90°C
Wire Size AWG N/A

Electrical

Current - Maximum per Contact 16.0A
Voltage - Maximum 250V AC / 300V DC

Material Info

Engineering Number C25200N2TSN

Reference - Drawing Numbers

Packaging Specification PK-121204-C25-001
Product Specification PS-121201-001-001
Sales Drawing SD-121204-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

**Compliant with
Exemption 6(c)**

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)

Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[121204 Series](#)