

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1212070004](#)
Status: **Active**
Overview: mPm DIN Valve Connectors
Description: mPm DIN Valve Connector, Form A-18mm, External Threads, 2 Pole Plus Ground with C4 Circuit, 24V, Red LED + VDR, Transparent, Integrated NBR Gasket, Single Bag, Unmounted



Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-121201-001-001 \(PDF\)](#)
[Product Specification STR-1251-001 \(PDF\)](#)
[Packaging Specification PK-121207-S28-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Field Attachable / Accessories
Series [121207](#)
Form A - 18mm
IP Rating IP67
Material - Contact Brass
Overview [mPm DIN Valve Connectors](#)
Product Name mPm
Type Field Attachable Connector
UPC 883906711610

Physical
Cable Diameter 4.00-9.00mm
Coupling Type External Thread
Diagnostics / LEDs Yes
Diagnostics Port No
Gender N/A
Keyway None
Material - Connector Body Polyamide
Material - Coupling Nut N/A
Material - Plating Mating Silver
Net Weight 20.171/g
Orientation 90° Angle
Pitch - Mating Interface 18.00mm
Poles 2
Temperature Range - Operating -40°C to +90°C
Wire Size AWG N/A

Electrical
Current - Maximum per Contact 16.0A
Voltage - Maximum 24V

Material Info
Engineering Number S28200TC420R

Reference - Drawing Numbers
[Packaging Specification](#) PK-121207-S28-001
[Product Specification](#) PS-121201-001-001, STR-1251-001
[Sales Drawing](#) SD-121207-001-001

EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/108/2014 (17 Dec 2014)	
Halogen-Free Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[121207 Series](#)