

3006102036

## EHS-2200

Rotary Light 220VAC

---



---

### DESCRIPTION

- Used in noisy areas to indicate a call
- Can be used for all Vingtor-Stentofon systems
- Used together with relay unit

Rotating beacon in painted mild steel housing, for less aggressive environments. Enduring with low noise friction-gear.

## SPECIFICATIONS

GENERAL	
Operating voltage	230VAC (50 - 60Hz) +- 10%
Lamp source	40 W Ba-15d
Rated current	200mA
Flash frequency	180 r.p.m
Operating temp	-10°C to +50°C
Material	Housing: Painted mild st. / Lens: PC
Housing Colour	Grey
Duty cycle	100%
Connection	1mtr. cable
IP-class	IP-54
Dimensions (mm)	148Ø x 215H
Weight	1.1 kg
Storage temp	-10°C to +55°C
Relative humidity	<95% Non-condensing
ORDER NUMBER	DESCRIPTION
3006102033	EHS-220B Rotary Light 220VAC Blue
3006102034	EHS-220G Rotary Light 220VAC Green
3006102035	EHS-220K Rotary Light 220VAC Clear
3006102036	EHS-220K Rotary Light 220VAC Orange
3006102037	EHS-220R Rotary Light 220VAC Red
ACCESSORIES	
3006102051	Spare Lens for EHS, Blue
3006102052	Spare Lens for EHS, Orange
3006102053	Spare Lens for EHS, Green
3006204181	Spare Lens for EHS, Clear
3006204182	Spare Lens for EHS, Red