

# **Home MultiRoom**

**SKU:** 470144 **MAP:** \$549.99

### **FEATURES**

- Stylish, MultiRoom-exclusive Inside Antenna.
- Powerful, precision-mount Outside Antenna.
- Enhances cell coverage for up to 3 large rooms.
- Tool-free installation. No need to drill holes.

★ WARNING: This product can expose you to chemicals including Nickel, which is known to the State of California to cause cancer, and Bisphenol A, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

### **About**

The weBoost **Home MultiRoom** cell signal booster boosts networks speeds across all available signal bands (including Band 25 for enhanced Sprint support) for up to three large rooms.


The Home MultiRoom also features an exclusive, Inside Antenna—featuring a built-in kickstand and stylish fabric cover while also providing best-in-class performance. Wall-mount installation is effortless with the included 3M® Command™ strips. The proprietary Outside Antenna offers a tool-free, finger-tightened precision mount. Users will experience faster data speeds, better voice quality, fewer dropped calls, and superior streaming capability. Home MultiRoom works with all US carriers—including Verizon, AT&T, T-Mobile, Sprint, and more.

It also comes with 2-year manufacturer's warranty, and 30-day money-back guarantee.

### Coverage Area

# IF THE CELL SIGNAL OUTSIDE YOUR BOOSTED CELL SIGNAL WILL COVER: Strong → Multiple Rooms Good → Large Room Weak → Medium Room None → None











### Kit Includes



Home MultiRoom



Power Supply (850018)



Outside Antenna Mounting Bracket



Outside Directional Antenna (314445)



15' (x2) & 30' Cables (YX030-15W), (950630)



Wall Mount Brackets w/Command Strips



Fabric Inside Panel Antenna (314440)








Cable Mounting Clips (x15)

### **Specifications**

MODEL NUMBER	470144 <sup>†</sup>	
FREQUENCIES	Band 12/17	700 MHz
	Band 13	700 MHz
	Band 5	850 MHz
	Band 4	1700/2100 MHz
	Band 25/2	1900 MHz
MAX GAIN	65 dB	
IMPEDANCE	75 Ohm	
POWER	110-240 V AC, 50-60 Hz, 8 W	
CONNECTORS	F-Female	
BOOSTER DIMENSIONS	6 x 6 x 1.6 in.	
BOOSTER WEIGHT	1.9 lbs.	



### Installation



- **Receives signal:** The outside antenna reaches out to access the existing strong outdoor cell signal and delivers it into the booster.
- **Boost signal:** The booster receives the signal, amplifies it, and serves as a relay between your phone and the nearest cell tower.
- Broadcasts signal: Your devices get a stronger signal, and calls and data are fed through the booster back to the network.

### **Available Accessories**



Plastic Inside Panel Antenna 314444



Lightning Surge Protector 75 Ohm 859992<sup>†</sup>



-3dB 2-Way Splitter 75 Ohm 850034\*



20 ft. White RG6 Low Loss Coax 950620\*



F-Female to F-Female Barrel Connector 971129\*

## Package Dimensions

9.313 L x 14 W x 11.375 H



FRONT

9.313 in. 11.375 in.

14 in. 9.313 in. SIDE



TOP/BOTTOM

WEIGHT

MASTER CARTON: 25.5 L x 19.5 W x 15.5 H | 43.8 lbs. | QTY 4

# Support



2-Year Warranty from Purchase.

Website: http://support.weboost.com

**Phone:** +1 866 294 1660 Monday to Saturday



**UPC** 



