



APC Rack PDU 9000 Switched, ZeroU, 20A, 208V, (21) C13/C15 & (3) C19/C21, L620 Cord

New

APDU9959NA3

Call for More Information 800-800-4272

- Includes: Installation guide, Rack mounting brackets, Safety guide

Output	
Nominal Output Voltage	200V, 208V
Overload Protection	No
Maximum Total Current Draw	16
Output Connections	(21) C13/C15 (3) C19/C21

Input	
Nominal Input Voltage	200V, 208V
Input frequency	50/60 Hz
Input Connections	IEC 60320 L6-20P
Acceptable Input Voltage	100 - 240VAC
Load Capacity	3300VA
Maximum Input Current	20A
Regulatory Derated Input Current (North America)	16A

Physical	
Maximum Height	70.75inches (1797MM, 179.7CM)
Maximum Width	2.17inches (55MM, 5.5CM)
Maximum Depth	1.81inches (46MM, 4.6CM)
Net Weight	12.37lbs. (5.61KG)
Shipping weight	17.33lbs. (7.86KG)
Shipping Height	78.82inches (2002MM, 200.2CM)

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.

Technical Specifications

Physical	
Shipping Width	6.5inches (165MM, 16.5CM)
Shipping Depth	4.49inches (114MM, 11.4CM)
Color	Black
Units per Pallet	48.0

Environmental	
Operating Temperature	23 - 140 °F (-5 - 60 °C)
Operating Relative Humidity	5 - 95 %
Operating Elevation	0 - 10000ft (0 - 3048meters)
Storage Temperature	-25 - 65 °C
Storage Relative Humidity	5 - 95 %
Storage Elevation	0 - 50000ft (0 - 15240meters)

Conformance	
Approvals	cUL listed, FCC part 15 class A, IEC 62368-1, PSE
Standard warranty	3 years repair or replace

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.