

# Network/server racks VX IT

with vented doors, with 482.6 mm (19") mounting angles, standard

Units U	Packs of	24	24	42	42	42	Page
Width mm		800	800	600	600	600	
Height mm		1200	1200	2000	2000	2000	
Depth mm		800	1000	600	800	1000	
Mounting position of the 482.6 mm (19") level(s)		front and rear	front and rear	front	front and rear	front and rear	
482.6 mm (19") attachment		on the cross-member, screw-fastened at the top and bottom	on depth stays, screw-fastened at the top and bottom	with mounting bracket screw-fastened to the frame at the top and bottom	with mounting bracket screw-fastened to the frame at the top and bottom	with mounting bracket screw-fastened to the frame at the top and bottom	
Max. load capacity (static) per enclosure N		8000	15000	7500	15000	15000	
Max. load capacity (static) per enclosure to UL 2416 N		8000	12000	6000	12000	12000	
Distance between prefitted 482.6 mm (19") levels mm		520	720	–	520	720	
Free mounting space to the 482.6 mm (19") level, front/rear mm		150 / 130	87 / 193	87 / 435	87 / 193	87 / 193	
Model No.	1 pc(s).	5303.114	5304.116	5329.111	5330.113	5308.113	
<b>Product-specific scope of supply, roof plate</b>							
Roof plate, multi-piece, with side cable entry in the depth, double-sided, prepared for fan mounting plate	1 pc(s).	■	■	–	–	–	
Roof plate, multi-piece, removable, for horizontal cable entry at the rear and with covered cut-out for fan mounting plate	1 pc(s).	–	–	■	–	–	
Roof plate, multi-piece, with cable entry in the corner sections front and rear	1 pc(s).	–	–	–	■	■	
<b>Product-specific scope of supply, door</b>							
Sheet steel door, vented, one-piece, 130° hinges	1 pc(s).	■	■	–	–	–	
Sheet steel rear door, vented, vertically divided, 180° hinges	1 pc(s).	–	–	■	■	■	
<b>Accessories</b>							
Side panel, screw-fastened, sheet steel	2 pc(s).	8175.245	8176.245	8106.245	8108.245	8100.245	901
Side panel, horizontally divided	1 pc(s).	–	–	–	–	5301.250	902
Baying connector, external, 3 mm	1 pc(s).	5301.310	5301.310	5301.310	5301.310	5301.310	914
Gland plate set, multi-piece, solid	1 pc(s).	5301.337	5301.344	–	–	5301.338	897

with vented doors, with 482.6 mm (19") mounting angles, standard

Units U	Packs of	42	42	42	42	47	Page
Width mm		600	800	800	800	600	
Height mm		2000	2000	2000	2000	2200	
Depth mm		1200	800	1000	1200	800	
Mounting position of the 482.6 mm (19") level(s)		front and rear	front and rear	front and rear	front and rear	front and rear	
482.6 mm (19") attachment		with mounting bracket screw-fastened to the frame at the top and bottom	on the cross-member, screw-fastened at the top and bottom	on depth stays, screw-fastened at the top and bottom	screw-fastened onto depth stays, top and bottom, and to the support rail on the frame structure	with mounting bracket screw-fastened to the frame at the top and bottom	
Max. load capacity (static) per enclosure N		15000	8000	15000	15000	15000	
Max. load capacity (static) per enclosure to UL 2416 N		12000	8000	12000	12000	12000	
Distance between prefitted 482.6 mm (19") levels mm		720	520	720	720	520	
Free mounting space to the 482.6 mm (19") level, front/rear mm		150 / 330	150 / 130	87 / 193	150 / 330	87 / 193	
Model No.	1 pc(s).	5310.118	5307.114	5309.116	5311.116	5331.113	
<b>Product-specific scope of supply, roof plate</b>							
Roof plate, multi-piece, with cable entry in the corner sections front and rear	1 pc(s).	■	–	–	–	■	
Roof plate, multi-piece, with side cable entry in the depth, double-sided, prepared for fan mounting plate	1 pc(s).	–	■	■	■	–	
<b>Product-specific scope of supply, door</b>							
Sheet steel rear door, vented, vertically divided, 180° hinges	1 pc(s).	■	■	■	■	■	
<b>Accessories</b>							
Side panel, screw-fastened, sheet steel	2 pc(s).	8102.245	8108.245	8100.245	8102.245	8128.245	901
Side panel, horizontally divided	1 pc(s).	5301.254	–	5301.250	5301.254	–	902
Baying connector, external, 3 mm	1 pc(s).	5301.310	5301.310	5301.310	5301.310	5301.310	914
Gland plate set, multi-piece, solid	1 pc(s).	5301.341	5301.337	5301.344	5301.347	–	897