



# APC EPDU1132M power distribution unit (PDU) 24 AC outlet(s) 0U Black

**Brand :** APC

**Product code:** EPDU1132M

**Product name :** EPDU1132M

EPDU1132M, Zero U, 32A, 230V, 20x C13, 4x C19, 1175x62x44 mm, Black  
 APC EPDU1132M. PDU types: Metered, Rack capacity: 0U, Type: Single-phase. AC outlets quantity: 24 AC outlet(s), AC outlet types: C13 coupler, C19 coupler, Power plug: IEC 60309. Certification: CE, TUV. Nominal input voltage: 200/208/230 V, Maximum current: 32 A, AC input frequency: 50/60 Hz. Width: 62 mm, Depth: 44 mm, Height: 1175 mm



<b>Design</b>		<b>Power</b>	
PDU types *	Metered	Maximum input current per phase	32 A
Type	Single-phase	<b>Weight &amp; dimensions</b>	
Rack capacity *	0U	Width	62 mm
Mounting	Vertical	Depth	44 mm
Housing material	Aluminium	Height	1175 mm
Product colour	Black	Weight	3.72 kg
Display	LCD	<b>Packaging data</b>	
On/off switch	✗	Package weight	4.48 kg
<b>Ports &amp; interfaces</b>		Package width	160 mm
AC outlets quantity *	24 AC outlet(s)	Package depth	110 mm
Power plug	IEC 60309	Package height	1320 mm
AC outlet types *	C13 coupler, C19 coupler	<b>Packaging content</b>	
<b>Features</b>		Manual	✓
LED indicators	✓	<b>Operational conditions</b>	
Certification	CE, TUV	Operating temperature (T-T)	-5 - 45 °C
<b>Management features</b>		Storage temperature (T-T)	-25 - 65 °C
Firmware upgradeable	✓	Operating relative humidity (H-H)	5 - 95%
<b>Power</b>		Storage relative humidity (H-H)	5 - 95%
Nominal input voltage *	200/208/230 V	Operating altitude	0 - 3000 m
AC input frequency	50/60 Hz	Non-operating altitude	0 - 15000 m
Maximum current *	32 A		
Nominal output voltage	230 V		
Load capacity	7360 VA		



731304405092

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.