

## APC EPDU1116B-SCH power distribution unit (PDU) 14 AC outlet(s) 0U Black

**Brand :** APC

**Product code:** EPDU1116B-SCH

**Product name :** EPDU1116B-SCH

EPDU1116B-SCH, ZeroU, 16A, 230V, 14x CEE 7, 902x62x44 mm, Black

APC EPDU1116B-SCH. PDU types: Basic, Rack capacity: 0U, Type: Single-phase. AC outlets quantity: 14

AC outlet(s), AC outlet types: Type F, Power plug: Type F. Cable length: 3 m, Certification: CE, TUV.

Nominal input voltage: 200/208/230 V, Maximum current: 16 A, AC input frequency: 50/60 Hz. Width: 62 mm, Depth: 44 mm, Height: 902 mm



Design		Power	
PDU types *	Basic	Maximum input current per phase	16 A
Type	Single-phase	Weight & dimensions	
Rack capacity *	0U	Width	62 mm
Mounting	Vertical	Depth	44 mm
Housing material	Aluminium	Height	902 mm
Product colour	Black	Weight	1.94 kg
On/off switch	✗	Packaging data	
Ports & interfaces		Package weight	2.84 kg
AC outlets quantity *	14 AC outlet(s)	Package width	160 mm
Power plug	Type F	Package depth	110 mm
AC outlet types *	Type F	Package height	1320 mm
Features		Packaging content	
Cable length	3 m	Manual	✓
Certification	CE, TUV	Operational conditions	
Power		Operating temperature (T-T)	-5 - 45 °C
Nominal input voltage *	200/208/230 V	Storage temperature (T-T)	-25 - 65 °C
AC input frequency	50/60 Hz	Operating relative humidity (H-H)	5 - 95%
Maximum current *	16 A	Storage relative humidity (H-H)	5 - 95%
Nominal output voltage	230 V	Operating altitude	0 - 3000 m
Load capacity	3680 VA	Non-operating altitude	0 - 15000 m



731304405030



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.