

APC Easy Rack 24U Freestanding rack Black

Brand : APC

Product code: ER6402

Product name : Easy Rack

Easy Rack 600mm/24U/1000mm , With Roof, Side panel, Castors, Feet, 4 Brackets, No Bottom, Black

[APC Easy Rack 24U Freestanding rack Black:](#)

Easy Racks are reliable and affordable IT enclosures with a proven design and essential features which is suitable for server rack and network rack applications, and edge computing applications.

APC Easy Rack. Type: Freestanding rack, Rack capacity: 24U, Maximum weight capacity: 1199.75 kg, Key lock, Adjustable feet, Castor wheels. Weight: 71.4 kg. Product colour: Black



Features		Weight & dimensions	
Rack capacity *	24U	Size (imperial)	48.3 cm (19")
Type *	Freestanding rack	Width	600 mm
Maximum weight capacity *	1199.75 kg	Depth	1000 mm
Maximum weight capacity (rolling)	599.65 kg	Height	1198 mm
Product colour	Black	Weight	71.4 kg
Front door construction	Double perforated	Mounting depth (min)	19.1 cm
Side panels included	✓	Mounting depth (max)	83.8 cm
Key lock	✓	Packaging data	
Back door key lock	✓	Package width	1050 mm
Front door key lock	✓	Package depth	650 mm
Adjustable feet	✓	Package height	1330 mm
Castor wheels	✓	Package weight	77 kg



731304433231

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 16-FEB-2022. Prints or copies of Information are only valid on the printed Publication date