



APC Rack PDU, Basic, 1U, 20A, 120V power distribution unit (PDU) Black

Brand : APC

Product code: AP9563

Product name : Rack PDU, Basic, 1U, 20A, 120V



Basic Rack PDU , Input: 120V , Input Connections: NEMA 5-20P , Cord Length: 12 feet (3.66 meters) , Output: 120V , Output Connections: NEMA 5-20R

APC Rack PDU, Basic, 1U, 20A, 120V power distribution unit (PDU) Black:

Rack-Mountable

Includes horizontal, vertical, and toolless-mount varieties. Puts power where it is needed most - in the racks near the equipment.

Single input power source

Supply power from one branch whip to multiple pieces of equipment, conveniently powering rack-mount equipment. Saves time and money during installation by using one branch whip and standard connections.

Wide range of input and output connections

Product family includes a variety of input and output connections to distribute 120V, 208V, or 230V power to multiple outlets. Having a variety of inputs and outputs allow users to adapt to varying power requirements. APC offers units that bring up to 14.4kW using a single branch whip.

Design		Power	
Product colour	Black	Nominal output voltage	120 V
Ports & interfaces		Load capacity	2400 VA
Input connection type	NEMA 5-20P	Maximum input current per phase	20 A
Output connections	10x NEMA 5-20R	Maximum total current draw per phase	20 A
Features		Weight & dimensions	
Cable length	3.66 m	Dimensions (WxDxH)	447 x 57 x 44 mm
Certification	cUL Recognized, CSA, UL 1363, UL Recognized, RoHS	Weight	2.5 kg
Power		Operational conditions	
Nominal input voltage *	120 V	Operating temperature (T-T)	-5 - 45 °C
AC input frequency	50 - 60 Hz	Storage temperature (T-T)	-25 - 65 °C



731304203889

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 01-MAR-2022. Prints or copies of Information are only valid on the printed Publication date