

APC AP5719 rack console 48.3 cm (19")

Brand : APC

Product code: AP5719

Product name : AP5719

19" Rack LCD Console

APC AP5719 rack console 48.3 cm (19"):

1U rack-mountable keyboard, mouse, LCD console and optional integrated KVM Switch.

Includes: C13-C14 power cord, Documentation CD, Firmware upgrade cable, Installation guide, NEMA 5-15 power cord, PS2 KVM cable, Rack mounting hardware, Single user rack mount kit, USB cable, USB KVM cable.

APC AP5719. Display diagonal: 48.3 cm (19"), Display: LCD. Interface: USB. Certification: C-tick, CCC, CE, EN 55022 A, EN 55024, EN 60950, FCC 15 A, GOST, IEC 60950, Industry Canada, KCC,.... Dimensions (WxDxH): 482 x 665 x 44 mm. Weight: 17.4 kg



Display		Certificates	
Display diagonal	48.3 cm (19")	Certification	C-tick, CCC, CE, EN 55022 A, EN 55024, EN 60950, FCC 15 A, GOST, IEC 60950, Industry Canada, KCC, NOM, UL, VCCI A, VDE
Display	LCD		
Technical details		Operational conditions	
Form factor	1U	Operating temperature (T-T)	0 - 40 °C
Power requirements	100 - 240 V, 50/60 Hz	Other features	
Ports & interfaces		Dimensions (WxDxH)	482 x 665 x 44 mm
Interface	USB	Weight & dimensions	
		Weight	17.4 kg
		Packaging data	
		Package weight	21 kg
		Package dimensions (WxDxH)	673 x 826 x 152 mm



731304283294

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-FEB-2022. Prints or copies of Information are only valid on the printed Publication date