

APC AP8941 power distribution unit (PDU) 24 AC outlet(s) 0U Black

Brand : APC

Product code: AP8941

Product name : AP8941

Rack PDU 2G, Switched, ZeroU, 30A, 200/208V, (21) C13 & (3) C19

APC AP8941. PDU types: Switched, Rack capacity: 0U, Product colour: Black. AC outlets quantity: 24 AC outlet(s), Power plug: NEMA L6-30P. Cable length: 3.05 m, Certification: cUL,FCC Part 15 A,ICES-003,PSE,UL,VCCI A. Nominal input voltage: 200-230 V, Maximum current: 30 A, AC input frequency: 50 - 60 Hz. Dimensions (WxDxH): 56 x 46 x 1829 mm, Weight: 7.64 kg



Design		Weight & dimensions	
PDU types *	Switched	Dimensions (WxDxH)	56 x 46 x 1829 mm
Rack capacity *	0U	Weight	7.64 kg
Product colour	Black	Packaging data	
Ports & interfaces		Package dimensions (WxDxH)	165 x 124 x 2040 mm
AC outlets quantity *	24 AC outlet(s)	Package weight	10 kg
Power plug	NEMA L6-30P	Operational conditions	
Features		Operating temperature (T-T)	-5 - 45 °C
Cable length	3.05 m	Storage temperature (T-T)	-25 - 65 °C
Certification	cUL,FCC Part 15 A,ICES-003,PSE,UL,VCCI A	Operating relative humidity (H-H)	5 - 95%
Power		Storage relative humidity (H-H)	5 - 95%
Nominal input voltage *	200-230 V	Operating altitude	0 - 3000 m
AC input frequency	50 - 60 Hz	Non-operating altitude	0 - 15000 m
Maximum current *	30 A	Technical details	
Nominal output voltage	208 V	Sustainability certificates	RoHS
Maximum total current draw per phase	30 A		
Power protection features	Overload		



731304277088

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-FEB-2022. Prints or copies of Information are only valid on the printed Publication date