

APC C13/C14 2.5m Black C14 coupler C13 coupler

Brand : APC

Product code: AP9870

Product name : C13/C14 2.5m



C13/C14, 2.5m, 90-250V, Black

APC C13/C14 2.5m. Cable length: 2.5 m, Connector 1: C14 coupler, Connector 2: C13 coupler. Input voltage: 90 - 250 V, Input current: 10 A



Features

Product colour *	Black
Connector 1 gender *	Male
Connector 2 gender *	Female
Cable length *	2.5 m
Connector 1 *	C14 coupler
Connector 2 *	C13 coupler
Connector 1 form factor	Straight
Connector 2 form factor	Straight
Overload protection	✘
Certification	CSA, UL, VDE, PEP, EOLI

Power

Input voltage	90 - 250 V
AC input frequency	50 - 60 Hz
Input current	10 A

Operational conditions

Operating temperature (T-T)	0 - 45 °C
Storage temperature (T-T)	-25 - 65 °C

Operational conditions

Operating relative humidity (H-H)	0 - 95%
Storage relative humidity (H-H)	0 - 95%
Operating altitude	0 - 3000 m
Non-operating altitude	15000

Sustainability

Sustainability certificates	RoHS
-----------------------------	------

Weight & dimensions

Width	76 mm
Depth	203 mm
Height	38 mm
Weight	230 g

Packaging data

Quantity per pack	1 pc(s)
Package width	102 mm
Package depth	203 mm
Package height	51 mm
Package weight	300 g



731304107897



999993750033

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.