

## APC Basic Rack PDU power distribution unit (PDU) 24 AC outlet(s) 0U Black

**Brand :** APC

**Product code:** AP7554

**Product name :** Basic Rack PDU

Rack PDU, Basic, ZeroU, 16A, 230V, (20)C13 & (4)C19; IEC309, 3m Cord

[APC Basic Rack PDU power distribution unit \(PDU\) 24 AC outlet\(s\) 0U Black:](#)

APC offers a wide variety of Basic Rack Power Distribution Units (PDUs) that distribute power to rack-mount equipment.

- Single input power source.
- Toolless Mounting Capabilities.
- Vertical Mounting Capabilities.

APC Basic Rack PDU. PDU types: Basic, Rack capacity: 0U, Mounting: Vertical. AC outlets quantity: 24 AC outlet(s), AC outlet types: C13 coupler, C19 coupler, Input connection type: IEC 309 16A. Cable length: 3.05 m, Certification: CCC, CE, VDE. Nominal input voltage: 230 V, Nominal output voltage: 230 V, Load capacity: 3680 VA. Dimensions (WxDxH): 56 x 44 x 1619 mm, Weight: 5.57 kg

Design		Power	
PDU types *	Basic	Maximum input current per phase	16 A
Rack capacity *	0U	Maximum total current draw per phase	16 A
Mounting	Vertical	Maximum power	3680 W
Product colour	Black		
Ports & interfaces		Weight & dimensions	
AC outlets quantity *	24 AC outlet(s)	Dimensions (WxDxH)	56 x 44 x 1619 mm
AC outlet types *	C13 coupler, C19 coupler	Weight	5.57 kg
Input connection type	IEC 309 16A		
Output connections	20x IEC 320 C13 4x IEC 320 C19		
Features		Packaging data	
Cable length	3.05 m	Package dimensions (WxDxH)	152 x 127 x 2134 mm
Certification	CCC, CE, VDE	Package weight	6.48 kg
Power		Operational conditions	
Nominal input voltage *	230 V	Operating temperature (T-T)	-5 - 45 °C
Nominal output voltage	230 V	Storage temperature (T-T)	-25 - 65 °C
Load capacity	3680 VA	Operating relative humidity (H-H)	5 - 95%
		Storage relative humidity (H-H)	5 - 95%

731304230397



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.