



APC RACK PDU. BASIC. ZERO U. 32A. 230V. (20)C13 & (4)C19 power distribution unit (PDU) 24 AC outlet(s) 0U Black

Brand : APC

Product code: AP7553

Product name : RACK PDU. BASIC. ZERO U. 32A. 230V. (20)C13 & (4)C19



Rack PDU, Basic, Zero U, 32A, 230V, (20)C13 & (4)C19

APC RACK PDU. BASIC. ZERO U. 32A. 230V. (20)C13 & (4)C19 power distribution unit (PDU) 24 AC outlet(s) 0U Black:

Features:

Single input power source

Toolless Mounting Capabilities

Vertical Mounting Capabilities

APC RACK PDU. BASIC. ZERO U. 32A. 230V. (20)C13 & (4)C19. PDU types: Basic, Rack capacity: 0U,

Type: Single-phase. AC outlets quantity: 24 AC outlet(s), AC outlet types: C13 coupler, C19 coupler,

Power plug: IEC 60309. Cable length: 3050 m. Nominal input voltage: 230 V, Nominal output voltage:

230 V, Output voltage: 230 V. Dimensions (WxDxH): 56 x 44 x 1619 mm, Weight: 5.57 kg

Design		Power	
PDU types *	Basic	Load capacity	7680 VA
Type	Single-phase	Maximum input current per phase	32 A
Rack capacity *	0U	Maximum total current draw per phase	32 A
Mounting	Vertical	Maximum power	7680 W
Product colour	Black		
Ports & interfaces		Weight & dimensions	
AC outlets quantity *	24 AC outlet(s)	Dimensions (WxDxH)	56 x 44 x 1619 mm
Power plug	IEC 60309	Weight	5.57 kg
AC outlet types *	C13 coupler, C19 coupler	Packaging data	
I/O ports	(20) IEC 320 C13 (4) IEC 320 C19 IEC 309 32A	Package dimensions (WxDxH)	152 x 127 x 2134 mm
Input connection type	IEC 309 32A	Package weight	6.48 kg
Output connections	(20) IEC 320 C13 (4) IEC 320 C19	Operational conditions	
Features		Operating temperature (T-T)	-25 - 65 °C
Cable length	3050 m	Storage temperature (T-T)	0 - 45 °C
Power		Operating relative humidity (H-H)	0 - 95%
Nominal input voltage *	230 V	Storage relative humidity (H-H)	0 - 95%
Nominal output voltage	230 V		
Output voltage	230 V		



731304225515

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 01-MAR-2022. Prints or copies of Information are only valid on the printed Publication date