



APC Basic Rack PDU AP7526 power distribution unit (PDU) 6 AC outlet(s) 1U Black

Brand : APC

Product code: AP7526

Product name : Basic Rack PDU AP7526

Basic Rack PDU AP7526

[APC Basic Rack PDU AP7526 power distribution unit \(PDU\) 6 AC outlet\(s\) 1U Black:](#)

Features:

- High Power Density.
- Horizontal mounting capability.
- Low Cost Power Distribution.

APC Basic Rack PDU AP7526. PDU types: Basic, Rack capacity: 1U, Mounting: Horizontal. AC outlets quantity: 6 AC outlet(s), AC outlet types: C19 coupler, Input connection type: IEC 309 32A 3P+N+PE. Cable length: 2.44 m, Certification: CE,GOST,VDE. Nominal input voltage: 400 V, Nominal output voltage: 230 V, Load capacity: 22080 VA. Dimensions (WxDxH): 437 x 254 x 44 mm, Weight: 4.84 kg



Design		Power	
PDU types *	Basic	Maximum input current per phase	32 A
Rack capacity *	1U	Maximum total current draw per phase	32 A
Mounting	Horizontal	Maximum power	22080 W
Product colour	Black		
Ports & interfaces		Weight & dimensions	
AC outlets quantity *	6 AC outlet(s)	Dimensions (WxDxH)	437 x 254 x 44 mm
AC outlet types *	C19 coupler	Weight	4.84 kg
Input connection type	IEC 309 32A 3P+N+PE		
Output connections	IEC 320 C19	Packaging data	
Features		Package dimensions (WxDxH)	559 x 502 x 241 mm
Cable length	2.44 m	Package weight	6.98 kg
Certification	CE,GOST,VDE	Operational conditions	
Power		Operating temperature (T-T)	-5 - 45 °C
Nominal input voltage *	400 V	Storage temperature (T-T)	-25 - 65 °C
Nominal output voltage	230 V	Operating relative humidity (H-H)	5 - 95%
Load capacity	22080 VA	Storage relative humidity (H-H)	5 - 95%



731304232667

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-FEB-2022. Prints or copies of Information are only valid on the printed Publication date