

APC AP8712S power cable Black 0.6 m

Brand : APC

Product code: AP8712S

Product name : AP8712S

Power Cord Kit (6 ea), Locking, C19 to C20, 0.6m

APC AP8712S power cable Black 0.6 m:

Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads.

APC AP8712S. Cable length: 0.6 m. Input current: 16 A



Features		Operational conditions	
Product colour *	Black	Storage relative humidity (H-H)	20 - 80%
Connector 1 gender *	Male	Operating altitude	0 - 3000 m
Connector 2 gender *	Female	Non-operating altitude	0 - 15000 m
Cable length *	0.6 m	Weight & dimensions	
Power		Weight	1.12 kg
Input current	16 A	Packaging data	
Operational conditions		Package width	60 mm
Operating temperature (T-T)	0 - 75 °C	Package height	300 mm
Storage temperature (T-T)	-25 - 75 °C	Package weight	1.12 kg
Operating relative humidity (H-H)	20 - 80%	Other features	
		Dimensions (WxDxH)	60 x 65 x 300 mm



731304279686



804904215689

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.