



# APC AP8981 power distribution unit (PDU) 24 AC outlet(s) 0U Black



**Brand :** APC

**Product code:** AP8981

**Product name :** AP8981

Rack PDU 2G, Switched, ZeroU, 11kW, 230V, (21) C13 & (3) C19

[APC AP8981 power distribution unit \(PDU\) 24 AC outlet\(s\) 0U Black:](#)

APC Switched Rack PDU , Input: 400V 3PH , Input Connections: IEC 309 16A 3P+N+PE, IEC 309 20A 3P+N+E , Cord Length: 6 feet ( 1.83 meters ) , Output: 208V, 230V , Output Connections: IEC 320 C13, IEC 320 C19.

Includes: Installation guide, Rack Mounting brackets, Safety guide, Sample locking IEC power cord, Serial configuration cable.

APC AP8981. PDU types: Metered, Switched, Rack capacity: 0U, Product colour: Black. AC outlets quantity: 24 AC outlet(s), Input connection type: IEC 309 16A 3P+N+PE, IEC 309 20A 3P+N+E, Output connections: (21) IEC 320 C13, (3) IEC 320 C19. Cable length: 1.83 m. Nominal input voltage: 400 V, AC input frequency: 50 - 60 Hz, Maximum input current per phase: 20 A. Dimensions (WxDxH): 56 x 46 x 1791 mm, Weight: 7 kg



Design		Power	
PDU types *	Metered, Switched	Maximum total current draw per phase	20 A
Rack capacity *	0U	Weight & dimensions	
Product colour	Black	Dimensions (WxDxH)	56 x 46 x 1791 mm
Ports & interfaces		Weight	7 kg
AC outlets quantity *	24 AC outlet(s)	Packaging data	
Input connection type	IEC 309 16A 3P+N+PE, IEC 309 20A 3P+N+E	Package dimensions (WxDxH)	165 x 114 x 2002 mm
Output connections	(21) IEC 320 C13, (3) IEC 320 C19	Package weight	8.95 kg
Features		Operational conditions	
Cable length	1.83 m	Operating temperature (T-T)	-25 - 65 °C
Power		Storage temperature (T-T)	-5 - 45 °C
Nominal input voltage *	400 V	Operating relative humidity (H-H)	5 - 95%
AC input frequency	50 - 60 Hz	Storage relative humidity (H-H)	5 - 95%
Maximum input current per phase	20 A		



731304277187

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.