

APC AP8858 power distribution unit (PDU) 20 AC outlet(s) 0U Black

Brand : APC

Product code: AP8858

Product name : AP8858

Rack PDU 2G, Metered, ZeroU, 20A/208V, 16A/230V, (18) C13 & (2) C19

[APC AP8858 power distribution unit \(PDU\) 20 AC outlet\(s\) 0U Black:](#)

APC Metered Rack Power Distribution Units (PDUs) provide active metering to enable energy optimization and circuit protection. User-defined alarm thresholds mitigate risk with real-time local and remote alerts to warn of potential circuit overloads. Metered Rack PDUs provide power utilization data to allow Data Center Managers to make informed decisions on load balancing and right sizing IT environments to lower total cost of ownership. Metered Rack PDUs include real power monitoring, a temperature/humidity sensor port, locking IEC receptacles, and ultra low profile circuit breakers. Users can access and configure Metered Rack PDUs through secure Web, SNMP, or Telnet Interfaces which are complimented by APC Centralized Management platforms using InfraStruxure Central, Operations, Capacity, and Energy Efficiency.



Design		Power	
PDU types *	Metered	Maximum input current per phase	16 A
Rack capacity *	0U	Maximum total current draw per phase	16 A
Mounting	Vertical	Maximum power	3680 W
Product colour	Black		
Ports & interfaces		Weight & dimensions	
AC outlets quantity *	20 AC outlet(s)	Dimensions (WxDxH)	56 x 44 x 902 mm
AC outlet types *	C13 coupler, C19 coupler	Weight	2.93 kg
Input connection type	IEC-320 C20	Packaging data	
Output connections	18x IEC 320 C13 2x IEC 320 C19	Package dimensions (WxDxH)	162 x 107 x 1124 mm
Features		Package weight	4.2 kg
Certification	CSA C22.2 No. 60950, IEC 60950, METI Denan, UL 60950-1, VDE RoHS, REACH	Operational conditions	
Management features		Operating temperature (T-T)	5 - 45 °C
Monitoring	Current, Power, Voltage	Storage temperature (T-T)	-25 - 65 °C
Power		Operating relative humidity (H-H)	5 - 95%
Nominal input voltage *	230 V	Storage relative humidity (H-H)	5 - 95%
AC input frequency	50 - 60 Hz		
Load capacity	3680 VA		



731304277026

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.