

## APC AP7821B power distribution unit (PDU) 8 AC outlet(s) 0U/1U Black



**Brand :** APC

**Product code:** AP7821B

**Product name :** AP7821B

208/230 V, 8x IEC 320 C13, IEC-320 C20, 1U, 444 x 102 x 44 mm, 1740 g  
APC AP7821B. PDU types: Metered, Rack capacity: 0U/1U, Mounting: Horizontal/Vertical. AC outlets quantity: 8 AC outlet(s), AC outlet types: C13 coupler, Power plug: C20 coupler. Certification: cUL, C-tick, CE, CSA, FCC 15 A, GOST, ICES-003, UL 60950, UL Listed, VCCI, VDE. Monitoring: Current, Power, Voltage. Nominal input voltage: 200-230 V, Maximum current: 20 A, AC input frequency: 50 - 60 Hz



Design		Power	
PDU types *	Metered	Maximum total current draw per phase	16 A
Rack capacity *	0U/1U	Maximum power	3680 W
Mounting	Horizontal/Vertical	Weight & dimensions	
Product colour	Black	Dimensions (WxDxH)	444 x 102 x 44 mm
Ports & interfaces		Weight	1.74 kg
AC outlets quantity *	8 AC outlet(s)	Packaging data	
Power plug	C20 coupler	Package dimensions (WxDxH)	470 x 337 x 64 mm
AC outlet types *	C13 coupler	Package weight	2.92 kg
Input connection type	IEC-320 C20	Packaging content	
Features		Packaging content	Cord Retention Bracket(s), Installation Guide, Rack Mounting Brackets, User Manual
LED indicators	✓	Operational conditions	
Certification	cUL, C-tick, CE, CSA, FCC 15 A, GOST, ICES-003, UL 60950, UL Listed, VCCI, VDE	Operating temperature (T-T)	-5 - 45 °C
Management features		Storage temperature (T-T)	-25 - 65 °C
Monitoring	Current, Power, Voltage	Operating relative humidity (H-H)	5 - 95%
Power		Storage relative humidity (H-H)	5 - 95%
Nominal input voltage *	200-230 V	Operating altitude	0 - 3000 m
AC input frequency	50 - 60 Hz	Non-operating altitude	0 - 15000 m
Maximum current *	20 A	Technical details	
Output voltage	230 V	Sustainability certificates	RoHS
Load capacity	3680 VA		
Maximum input current per phase	16 A		



731304331513

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 25-FEB-2022. Prints or copies of Information are only valid on the printed Publication date