

Rack PDU, Switched, 1U, 16A, 208/230V, (8)C13

AP7921B

In Stock

\$709.00*

- Switched Rack Power Distribution Units (PDUs) provide advanced load monitoring combined with remote on/off switching control of individual outlets for power cycling, delayed power sequencing, and outlet use management.
- Includes: Installation Guide, Rack Mounting Brackets, User Manual

Output	
Nominal Output Voltage	208V, 230V
Maximum Total Current Draw	16
Output Connections	(8) IEC 320 C13 (Battery Backup)

Input	
Nominal Input Voltage	200V, 208V, 230V
Input frequency	50/60 Hz
Input Connections	IEC-320 C20
Cord Length	8.2ft (2.5meters)
Acceptable Input Voltage	200-240VAC
Number of Power Cords	1
Load Capacity	3680VA
Maximum Input Current	20A
Regulatory Derated Input Current (North America)	16A

Physical	
Maximum Height	1.73inches (44MM, 4.4CM)
Maximum Width	17.5inches (445MM, 44.5CM)
Maximum Depth	4.25inches (108MM, 10.8CM)
Rack Height	1U
Net Weight	5.0lbs. (2.27KG)

*Prices are indicative

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.

Technical Specifications

Physical	
Shipping weight	7.6lbs. (3.45KG)
Shipping Height	2.75inches (70MM, 7.0CM)
Shipping Width	18.5inches (470MM, 47.0CM)
Shipping Depth	13.5inches (343MM, 34.3CM)
Color	Black

Environmental	
Operating Temperature	32 - 113 °F (0 - 45 °C)
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-10000ft (0-3000meters)
Storage Temperature	-25 - 65 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-50000ft (0-15000meters)

Conformance	
Approvals	cUL Listed, CE, CSA, EN 55022 Class A, EN 55024, EN 61000-3-2, EN 61000-3-3, GOST, IRAM, MIC, UL 60950, UL Listed, VDE, VCCI
Standard warranty	2 years repair or replace

Sustainable Offer Status	
RoHS	Compliant
REACH	REACH: Contains No SVHCs
Battery Directive	Compliant
Proposition 65 Warning	Available in Documentation tab

*Prices are indicative

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.