



## APC AP4450 power distribution unit (PDU) 10 AC outlet(s) 1U Black

Brand : APC

Product code: AP4450



Product name : AP4450

Rack ATS, 100-120 V, 15 A, (10) NEMA 5-15R, Black

APC AP4450. PDU types: Switched, Rack capacity: 1U, Mounting: Horizontal. AC outlets quantity: 10 AC outlet(s), AC outlet types: NEMA 5-15R. Nominal input voltage: 100-120 V, Maximum current: 15 A, AC input frequency: 50 - 60 Hz. Dimensions (WxDxH): 44 x 236 x 432 mm, Weight: 4.4 kg

Design		Power	
PDU types *	Switched	Maximum total current draw per phase	15 A
Rack capacity *	1U	<b>Weight &amp; dimensions</b>	
Mounting	Horizontal	Dimensions (WxDxH)	44 x 236 x 432 mm
Product colour	Black	Weight	4.4 kg
Ports & interfaces		Operational conditions	
AC outlets quantity *	10 AC outlet(s)	Operating temperature (T-T)	-5 - 45 °C
AC outlet types *	NEMA 5-15R	Storage temperature (T-T)	-25 - 65 °C
Power		Operating relative humidity (H-H)	0 - 95%
Nominal input voltage *	100-120 V	Storage relative humidity (H-H)	0 - 95%
AC input frequency	50 - 60 Hz	Operating altitude	0 - 3000 m
Maximum current *	15 A	Non-operating altitude	0 - 15000 m
Nominal output voltage	100-120 V		
Load capacity	1440 VA		



731304333494

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.