



## APC AP7911B power distribution unit (PDU) 16 AC outlet(s) 2U Black


Brand : APC

Product code: AP7911B

Product name : AP7911B



Switched, 2U, 30A, 208V, 16x C13, NEMA L6-30P, 444 x 254 x 89 mm, 6320 g  
APC AP7911B. PDU types: Switched, Rack capacity: 2U, Product colour: Black. AC outlets quantity: 16 AC outlet(s), AC outlet types: C13 coupler, Input connection type: NEMA L6-30P. Cable length: 3.66 m, Certification: cUL, CSA, FCC 15 A, ICES-003, PSE, UL 60950, UL. Monitoring: Current, Outlet control: Recycle, Turn off. Nominal input voltage: 200-230 V, Maximum current: 30 A, AC input frequency: 50 - 60 Hz



<b>Design</b>		<b>Power</b>	
PDU types *	Switched	Maximum input current per phase	30 A
Rack capacity *	2U	Maximum total current draw per phase	30 A
Product colour	Black		
<b>Ports &amp; interfaces</b>		<b>Weight &amp; dimensions</b>	
AC outlets quantity *	16 AC outlet(s)	Dimensions (WxDxH)	444 x 254 x 89 mm
AC outlet types *	C13 coupler	Weight	6.32 kg
Input connection type	NEMA L6-30P		
<b>Features</b>		<b>Packaging data</b>	
LED indicators	✓	Package dimensions (WxDxH)	514 x 514 x 146 mm
Cable length	3.66 m	Package weight	8.36 kg
Certification	cUL, CSA, FCC 15 A, ICES-003, PSE, UL 60950, UL	<b>Operational conditions</b>	
<b>Management features</b>		Operating temperature (T-T)	0 - 45 °C
Monitoring	Current	Storage temperature (T-T)	-25 - 65 °C
Outlet control	Recycle, Turn off	Operating relative humidity (H-H)	0 - 95%
<b>Power</b>		Storage relative humidity (H-H)	0 - 95%
Nominal input voltage *	200-230 V	Operating altitude	0 - 3000 m
AC input frequency	50 - 60 Hz	Non-operating altitude	0 - 15000 m
Maximum current *	30 A	<b>Technical details</b>	
		Sustainability certificates	RoHS



731304331605

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.