

APC NetShelter CX 24U Freestanding rack Black

Brand : APC

Product code: AR4024IX429

Product name : NetShelter CX

NetShelter CX 24U 750 mm Wide x 1130 mm Deep Enclosure Black

[APC NetShelter CX 24U Freestanding rack Black:](#)

Specialized enclosures with integrated cooling, noise dampening, and power distribution for server and network applications in office environments.

APC NetShelter CX. Type: Freestanding rack, Rack capacity: 24U, Maximum weight capacity: 805 kg. Power supply: 68 W. International Protection (IP) code: IP44. Weight: 154.5 kg. Product colour: Black



Features		Power	
Rack capacity *	24U	AC input frequency	50 - 60 Hz
Type *	Freestanding rack	Weight & dimensions	
Maximum weight capacity *	805 kg	Size (imperial)	48.3 cm (19")
Product colour	Black	Width	750 mm
Cooling type	Active	Depth	1130 mm
International Protection (IP) code	IP44	Height	1275 mm
Certification	RoHS, REACH	Weight	154.5 kg
Power		Packaging data	
Power supply	68 W	Package width	800 mm
AC input voltage	200 - 240 V	Package depth	1200 mm
		Package height	1490 mm
		Package weight	181.7 kg



731304298137

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 24-FEB-2022. Prints or copies of Information are only valid on the printed Publication date