



C-USB3/AB

USB 3.0 A (M) to B (M) Cable



Kramer's C-USB3/AB is a SuperSpeed USB 3.0 Type-A male to Type-B male cable used to connect computers and peripherals, such as printers, scanners, cameras, keyboards, mice and other digital devices for superior signal transfer of up to 4.8Gbps

FEATURES

USB 3.0 A Male to B Male

Transfer Rates up to 4.8Gbps - 10x the capability of USB 2.0

Foil & Overall Braid Provide Maximum Protection Against EMI/RFI

Molded Strain Relief

Backward Compatibility - USB Specifications 1.0, 1.1 and 2.0

RoHS Compliant

Varied Selection of Lengths - Available in versions of 3 to 6ft (0.9 to 1.8m)



TECHNICAL SPECIFICATIONS

OVERALL	TYPE: USB 3.0 SuperSpeed
	MAX. DATA RATE: 4.8 Gbps
PHYSICAL	CONNECTOR A: USB 3.0 type-A male
	CONNECTOR B: USB 3.0 type-B male
	CONNECTOR PLATING: Nickel
	CONDUCTORS: 28/24AWG
	CABLE SHIELD TYPE: Aluminum-Mylar Foil with Braid
	OVERALL SHEATH DIAMETER: 5.5mm
REGULATORY	OUTER SHEATH COLOR: Blue
	STANDARDS: 2011/65/EU



CONFIGURATIONS

C-USB3/AB-3	USB 3.0 A (M) to B (M) Cable
C-USB3/AB-6	USB 3.0 A (M) to B (M) Cable