



BC6A-LS203

CAT6A U/FTP 650MHz 4x2x23AWG Bulk
Cable – Low Smoke & Halogen Free



Kramer's BC6A-LS203 bulk cable is a high-quality CAT6A U/FTP low smoke & halogen free four pair twisted cable, designed for LAN applications that ensures optimum performance

FEATURES

Quality Construction - 4 shielded twisted pairs (U/FTP) of 23AWG solid copper conductors are cabled together in an unshielded outer LSHF jacket

Performance - Tested up to 650MHz

RJ-45 Connector - The larger diameter 23AWG twisted pair cable requires a special RJ-45 connector. Use the K-LAN CON-RJ45-3

Ideal for 10GbE and legacy speeds applications

Length - Available in wooden drums of 305/500m (1000/1640ft)



TECHNICAL SPECIFICATIONS

CONDUCTORS	Size: 4x2x23AWG Material: Annealed copper Diameter: 0.56mm $\pm$ 0.01mm
INSULATION	Material: Skin/Foam/Skin HDPE Diameter: 1.33mm $\pm$ 0.10mm Color Code: White/Blue, White/Orange, White/Green, White/Brown
SCREENING	Material: Alu/PET per pair (Alu side out)
DRAIN WIRE	Material: Tinned copper Diameter: 0.4mm $\pm$ 0.01mm
JACKET	Material: LSHF Color: Yellow RAL 1018 Thickness: $\geq$ 0.5mm Diameter: 7.2mm $\pm$ 0.2mm
ELECTRICAL	Impedance: 1–100MHz: 100 Ω $\pm$ 15 Ω , 100–250MHz: 100 Ω $\pm$ 20 Ω , 250–500MHz: 100 Ω $\pm$ 25 Ω Propagation Velocity (NVP): 76% Voltage Rating: 30V Delay Skew: <45ns Mutual Pair Capacitance: $\leq$ 42pF/m Capacitance Unbalance Pair/ground: $\leq$ 1500pF/km Conductor DC Resistance: <79.8 Ω /km Pair Resistance Unbalance DC: <1.5% Dielectric Strength: 2.5kV DC (2s) Insulation Resistance (500V): >5000M Ω /km
USAGE AND ENVIRONMENTAL	Storage / Transport / Installation Temperature: 0°C to +50°C Operation Temperature: –20°C to +60°C
MECHANICAL	Maximum Pulling Tension: 100N Bending Radius - Installed: 50mm Bending Radius - During Installation: 60mm
STANDARDS COMPLIANCE	Electrical: EIA/TIA 568A, ISO/IEC 11801 Fire Performance: IEC 60332-1 Smoke Density: IEC 61034

Halogen Free: IEC 60754

RoHS: 2011/65/EU



CONFIGURATIONS

BC6A-LS203-D305M	CAT6A U/FTP 650MHz 23AWG Bulk Cable – Low Smoke & Halogen Free
------------------	--

BC6A-LS203-D500M	CAT6A U/FTP 650MHz 23AWG Bulk Cable – Low Smoke & Halogen Free
------------------	--