

SOLID PC 3819 13 T



Sample photo

Order symbol: PC 3819 13 T
Product nbr: 5330061
Description: Enclosure, PC
Remarks: Transparent cover

EAN: 6418074005472
El. number:
 Finland 3423809
 Italy 7402030
 Sweden 2539444

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

| Dimensions: | | L | W | H | Rating: |
|-------------------------------|--|----------------------|-----|--|---|
| mm: | | 378 | 188 | 130 | Electrical insulation: Totally insulated |
| inch: | | 14.9 | 7.4 | 5.1 | Halogen free (DIN/VDE 0472, Part 815): Yes |
| Materials: | | | | | UV resistance: UL 508 |
| Material: | | Polycarbonate | | Flammability Rating (UL 746 C 5): UL 94 5V | |
| Gasket material: | | Polyurethane | | Glow Wire Test (IEC 695-2-1) °C: 960 | |
| Base colour: | | RAL 7035 | | NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12 | |
| Cover colour: | | Clear transparent | | Ingress Protection (EN 60529): IP 66/67 | |
| Cover screws material: | | Polyamide | | Impact Resistance (EN 50102): IK 08/09 | |
| Cover screws colour: | | Grey | | Certificates: | |
| Temperatures: | | | | | Underwriters Laboratories |
| Short term: | | -40 ... 120 °C | | Canadian Standards Association | |
| Continuous: | | -40 ... 80 °C | | Fimko | |
| Short term: | | -40 ... 250 °F | | Europe EN 50298: 1998 | |
| Continuous: | | -40 ... 175 °F | | UL Canada | |
| Accessories: | | | | | Gost R |
| EKMVT | | Mounting plate | | | |
| EKV 12 | | DIN-35 Mounting rail | | | |
| EKV 32 | | DIN-35 Mounting rail | | | |
| EKMZR | | Extension frame | | | |

