



NOTES:

1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. TERMINATED WITH (8 POSITION) MODULAR PLUG ON ONE END AND A (8 POSITION) MODULAR JACK ON THE OTHER END PER THE WIRE MAP DESCRIBED IN TABLE 1.
3. CONSTRUCTED WITH 28 AWG SOLID CONDUCTOR CATEGORY 6A F/UTP HALOGEN FREE (CM/LSZH) PATCH CABLE.
4. MATERIALS:
 PLUG: POLYCARBONATE
 CONTACTS AND IDCs: GOLD PLATED PHOSPHOR BRONZE
 JACK HOUSING: ABS
5. NOMINAL CABLE DIAMETER: 0.185IN [4.7]
6. CABLE JACKET COLOR: BLACK
7. WEIGHT: 0.44LB/10 PCS [198g/ 10 PCS]
8. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIALS RESTRICTIONS OF RoHs, (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHs TECHICAL ADAPTATION COMMITTEE.

TABLE 1: WIRING SCHEME

PLUG		JACK	
WIRED TO THE T568 'B' WIRING SCHEME			
POSITION	CONDUCTOR COLOR	POSITION	CONDUCTOR COLOR
1	WHITE/ORANGE	1	WHITE/BLUE
2	ORANGE	2	ORANGE
3	WHITE/GREEN	3	CONDUCTOR CUT
4	BLUE	4	CONDUCTOR CUT
5	WHITE/BLUE	5	CONDUCTOR CUT
6	GREEN	6	CONDUCTOR CUT
7	WHITE/BROWN	7	WHITE/GREEN
8	BROWN	8	CONDUCTOR CUT

PART NUMBER		MA024	
TITLE			
G5 PDU TO G3 GATEWAY SERIAL ADAPTER			
CUSTOMER DRAWING			
ITEM REVISION NAME		00266NAB/01	
DATASET FILE NAME		00266NAB_DC02/01A	
		THIRD ANGLE PROJECTION	
MATERIAL		SEE NOTE 4	
DRAWING NUMBER		00266NAB-02	
DRAWN BY	DATE	CHK	SCALE
BSN	7-24-20	DJB	NONE
SHEET 1 OF 1		A	

01A	10-21-20	BSN	DJB	DIJ	RELEASED TO PRODUCTION	00266NAB-02
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

A-SIZE CUSTOMER