



Rapier Sounders

High Quality Stainless Steel External Sounders

- · Designed to meet the requirements of EN50131-4:2009 Grade 3 and 4
- Environmental class IV
- Low power operation: 10mA standby, 180mA full alarm (siren & strobe)
- · Battery and Piezo self-test with fault output
- · Remote test input
- · Ring line monitoring
- · Silent engineer mode
- · Range of selectable integral EOL tamper resistors
- · Can be mounted portrait or landscape
- · Audible tamper closure to assist commissioning
- · LED strobe
- Twin flashing comfort LEDs
- Full SAB capability
- · Selectable positive hold-off signalling
- · Diagnostic LED
- · Cascade tamper for multiple sounder installations
- · Drill detection (G4S model only)
- · Two internal spirit levels to aid vertical or horizontal mounting
- 3 Year warranty



DESCRIPTION

The Rapier range of sounders are designed to work as part of Intruder systems.


This range of stainless steel external sounders fully meet the requirements of EN50131-4:2019 Grade 3 and 4. They include a diagnostic LED which will flash to indicate problems with the sounder, versatile trigger options and comfort LEDs to signal that the device is working. Control panel dependent end of line resistors also help make installation easier.

The Rapier sounders can be mounted in portrait or landscape orientation, giving real flexibility. This is now made easier with the inclusion of two internal spirit levels. The stainless steel cover's clean lines gives a smart and sleek look to the unit.



APPROVALS EN50131-4:2009 PD6662:2017 UKCA | CE Mark

TECHNICAL SPECIFICATIONS



See next page for ordering information and product details







ORDERING INFORMATION



PART NO

RAPIER-G3S

PART NO

RAPIER-G4S

PART NO

RAPIER-DUM-SS

DESCRIPTION

Galvanised steel backplate Stainless steel cover Grade 3 L 342mm x W 221mm x D 55mm 3.75kg

DESCRIPTION

Galvanised steel backplate Stainless steel cover Grade 4 L 342mm x W 221mm x D 55mm 3.75kg

DESCRIPTION

Dummy cover with bracket Stainless steel cover L 342mm x W 221mm x D 55mm