

Eaton MBP6KI

Catalog Number: MBP6KI

Eaton HotSwap MBP maintenance bypass, 6000 VA, Input: Hardwired, 200-240V, Outlets: (3) C13, (2) C19, Hardwired

General specifications



Product Name

Eaton HotSwap MBP maintenance bypass

UPC

743172040145

Product Height

150 mm

Product Weight

3.28 kg

Certifications

CE

Catalog Number

MBP6KI

Model Code

Eaton HotSwap MBP 6000i

Product Length/Depth

185 mm

Product Width

305 mm

Compliances

CE Marked

Type

Hotswap MBP

Form factor

3U

Outlet control

No

Package contents

Maintenance Bypass
Cable locking system
Connection cable to the
UPS
Rack-mounting kit
User manual

Operating Temperature

0° to 40°C (32° to 104°F)

Mounting direction

Horizontal

Color

Black

Input connection

Other

VA rating

6000 VA

Input voltage

200-240V

Phase

Single-phase

Outlets

(3) C13, (2) C19, Hardwired

Number of Outputs C13

3

Number of Outputs C19

3

Number of outputs hardwired

1

Brochures

Eaton UPS Services Quick Guide - EN

Eaton UPS and battery services - EN

Compliance information

EU declaration of conformity Eaton 9PX UPS

Number of outlets with earth pin

5

SNMP

No

Ethernet interface

No

Serial interface

No

Mass configuration

No

Electrical connection

Screwed terminal

Mounting Dimension (metrical)

150

Mounting dimension (standardized)

482.6 mm (19 inch)

Switchable

No

Over voltage category

2

Fitted with:

Mounting material

LED indication

Communication

No