

# Eaton 9SX5KIRT

Catalog Number: 9SX5KIRT

Eaton 9SX UPS, 5000 VA, 4500 W, Input: Hardwired, Outputs: (8) C13, (2) C19, Hardwired, Rack/tower, 3U



## General specifications

Product Name	Catalog Number
Eaton 9SX UPS	9SX5KIRT
UPC	Product Length/Depth
743172039347	68.5 cm
Product Height	Product Width
13 cm	44 cm
Product Weight	Compliances
48 kg	CE Marked
	TUV
	cULus Listed
	CSA 22.2
Certifications	
IEC/EN 62040-1	
UL 1778	
IEC/EN 62040-2	
CE	
cULus Listed	
EAC	

## Battery

### Battery type

Sealed, lead-acid

### Runtime graph

\$row.attributeValue.cdata

### Battery replacement

Hot-swappable internal batteries and extended battery modules (EBMs)

### Battery quantity

15

### Battery management

ABM & Temperature  
compensated charging  
method (user selectable)  
Automatic battery test  
Deep discharge protection  
Automatic recognition of  
external battery units

### Battery rating

12 V / 5 Ah

### Extended battery capability

Yes

## Electrical output

### Receptacle

(8) C13, (2) C19, Hardwired

### Voltage

230V

### Wattage

4500 W

### Output power factor

0.9

### Output voltage range

200/208/220/230/240 V +/- 1%

### Output waveform

Sine wave

### Output nominal voltage

230V default (200/208/220/230/240V)

### Voltage distortion output (linear load) - max

2

### Feed type

1

### Topology

Online/Double-conversion

### VA rating

5000 VA

## Electrical input

### Input connection

Hardwired/fixed connection

### Input nominal voltage

230V default (200/208/220/230/240/250V)

### Nominal frequency

50/60 Hz

### Input power factor

>.99

### Input voltage range

176-276 V (100-276 V with derating)

## Communications

### Includes network card

No

### Communication

USB port (HID compliant)  
Serial port (RS232)  
Mini terminal block for  
remote On/Off  
Mini-terminal block for  
remote power off  
Dry contacts (4 outputs,  
relay, DB9)

#### Input frequency range

40-70 Hz

#### Ethernet interface

No

#### User interface

Multilingual graphical LCD display

#### Potential free switch contact

Yes

#### Expansion slots

One slot for optional communication card

#### Software compatibility

Eaton Intelligent Power Manager, Eaton Intelligent Power Protector

#### Type of interface

Other

### Environmental

#### Altitude

3000 m

#### Noise level

<45 dB at 1 meter

#### Temperature range

0° to 40°C (32° to 104°F)

#### Relative humidity

0-95% non-condensing

### Additional specifications

#### Construction type

482.6 mm (19 inch) device

#### Package contents

UPS  
(2) IEC-IEC output cables  
USB cable  
Serial cable  
(2) Supports for tower mounting  
(2) brackets for 19' mounting  
(2) Rack-mounting kit  
Cable locking system  
Safety instructions  
Quickstart guide

#### Phase (output)

1

#### Internal bypass

Yes

#### Auto shutdown function

Yes

#### Color

Black

#### Efficiency

Rack mounting kit

Yes

Phase (input)

1

Hot swap power

No

Resources

Brochures

Eaton UPS and battery services - EN

Eaton UPS Services Quick Guide - EN

Compliance information

EU declaration of conformity Eaton 9SX UPS

Manuals and user guides

Eaton 9SX-9PX UPS - 5-6 kVA-EBM 180V - Installation and user manual

Technical data sheets

Eaton 9SX UPS - 5/6/8/11 kVA - Datasheet



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All rights reserved.

Eaton is a registered trademark.  
  
All other trademarks are property of their respective owners.



Eaton.com/socialmedia