

# Eaton EILB13

Catalog Number: EILB13

Eaton G3+ In-line Metered Rack PDU, 0U, 10U, Input IEC-60309 16A 1Ph, 3.7 kW max, 16A, 200-240V, Outlets 1XIEC60309 16A

## General specifications



Product Name	Catalog Number
Eaton Rack PDU G4	EILB13
Model Code	UPC
EPDU IL 0U (309 16A 1P)1X309	743172065841
Product Length/Depth	Product Height
439 mm	52 mm
Product Width	Product Weight
53 mm	1.82 kg
Compliances	Certifications
CE Marked	CE
RoHS Compliant	IEC 60950-1
EAC	EN 55024:2010

### Special features

Phase Metering, Circuit Breaker Current Metering and Input Metering  
Hot-Swap Control module with advanced LCD  
Optional  
Temperature/Humidity sensor  
Daisy-Chain up to 8 PDUs, reduce network infrastructure costs  
Power chain monitoring & Real time Intelligence on your Data Center, via Eaton Intelligent Power Manager  
Trigger advanced actions including Vmware SRM and VM migration via Intelligent Power Manager IT software  
60°C Operating temperature  
Low-profile form factor: 52 mm wide x 53 mm deep on most models  
Mass configuration and update available via Intelligent Power Manager IT software

### Type

In-line metered Rack PDU

### Form factor

0U (Vertical)

### Outlet control

No

### Package contents

Rack PDU  
Mounting accessories  
Network cable  
Configuration cable  
Splitter for daisy-chaining  
Quickstart guide  
Safety Instructions

### Brochures

[Eaton UPS Services Quick Guide - EN](#)

[Eaton UPS and battery services - EN](#)

[Eaton ePDU G3 - Brochure](#)

### Compliance information

[EU Declaration of Conformity Eaton ePDUs G3](#)

### Declarations of conformity

[EU declaration of conformity Rack PDU G4](#)

### Drawings

[EILB13 sk-30919-y1](#)

### Manuals and user guides

[Eaton ePDU G3 - Installation and Connectivity Quick Start](#)

Operating Temperature

0° to 60°C (32° to 140°F)

Mounting direction

Vertical

Color

Black

Material

Aluminium

Input connection

IEC-60309 16A 1Ph

Cord length

3m

Wattage

3.84 kW max

Amperage Rating

16A

Input voltage

200-240V

Phase

Single-phase

Frequency rating

50/60 Hz

Outlets

(1) IEC60309 16A

Number of outputs (other)

1

Number of outlets with earth pin

1

SNMP

Yes

Ethernet interface

Yes

Serial interface

Yes

Mass configuration

Yes

Electrical connection

Connecting cord with plug

Mounting Dimension (metrical)

52

Mounting dimension (standardized)

Metric

Switchable

No

Over voltage category

2

Fitted with:

Ampere Meter

Mounting material

Display

Communication

HTTP, HTTPS, SSL, Telnet, FTP, SNMP, SMTP, DNS, DHCP,

LDAP, RADIUS

Series

G3+



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All rights reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)