

Eaton 9PX2200IRTBPB

Catalog Number: 9PX2200IRTBPB

Eaton 9PX UPS HotSwap BS, 2200 VA, 2200 W, Input: C20, Outputs: (3) BS, (1) C19, Rack/tower, 3U



General specifications

Product Name	Catalog Number
Eaton 9PX UPS	9PX2200IRTBPB
Model Code	UPC
Eaton 9PX 2200i RT3U HotSwap BS	743172081537
Product Length/Depth	Product Height
48.5 cm	13 cm
Product Width	Product Weight
44 cm	24.52 kg
Compliances	Certifications
TUV	IEC/EN 62040-1
CSA 22.2	CE
cULus Listed	UL 1778
CE Marked	ENERGY STAR certified
CISPR22 Class B	IEC/EN 62040-2
FCC part 15 Class B	EAC

Battery

Runtime graph

View runtime graph

Battery management

ABM & Temperature
compensated charging
method (user selectable)
Automatic battery test
Deep discharge protection
Automatic recognition of
external battery units

Battery replacement

Hot-swappable internal batteries and extended battery modules
(EBMs)

Battery quantity

6

Battery rating

12 V / 7 Ah

Battery type

Sealed, lead-acid

Extended battery capability

Yes

Electrical output

Receptacle

(3) BS, (1) C19

Topology

Online/Double-conversion

Wattage

2200 W

VA rating

2200 VA

Output waveform

Sine wave

Voltage

230V

Output power factor

1

Output nominal voltage

230V default (200/208/220/230/240V)

Output voltage range

200/208/220/230/240 V +/- 1%

Voltage distortion output (linear load) - max

3

Output frequency

50/60 Hz

Feed type

1

Electrical input

Input connection

C20

Input cord length

1.8m

Input nominal voltage

230V default (200/208/220/230/240V)

Input voltage range

176-276 V (100-276 V with derating)

Communications

Communication

USB port (HID compliant)

Serial port (RS232)

Mini terminal block for
remote On/Off

Mini-terminal block for
remote power off

Mini-terminal block for
output relay

Dry contacts (3 outputs, 1

Nominal frequency

50/60 Hz

Input frequency range

40-70 Hz

Input power factor

>.99

input, optocoupler, DB9)

Expansion slots

One slot for optional communication card

Ethernet interface

No

Includes network card

No

Software compatibility

Eaton Intelligent Power Manager, Eaton Intelligent Power Protector

User interface

Multilingual graphical LCD display

Type of interface

Other

Potential free switch contact

Yes

Environmental

Altitude

3000 m

BTU Rating

Online: 488

Noise level

<40 dB at 1 meter

Relative humidity

0-96% non-condensing

Temperature range

0° to 40°C (32° to 104°F)

Additional specifications

Special features

Double conversion topology

Constantly monitors power conditions and regulates

voltage and frequency

First UPS in its class to provide Unity power factor (VA=W)

Energy Star qualified, provides the highest

efficiency level to reduce energy and cooling costs

Internal bypass allows service continuity in case of UPS fault

Next-generation graphical LCD display

Compatible with Virtual environments (VMware, Hyper-V, Citrix Xen, Redhat)

Meter energy consumption (down to the managed outlet

groups)
Hot swappable batteries
Advanced Battery
Management (ABM)
technology to increase
battery lifetime
Long backup time with up to
4 optional EBM

Form factor

Rack/tower

Rack size

3U

Construction type

482.6 mm (19 inch) device

Rack mounting kit

Yes

Efficiency

93.5

Package contents

UPS
Input cable
Maintenance Bypass
(2) IEC-IEC output cables
USB cable
Serial cable
(2) brackets for 19' mounting
(2) Rack-mounting kit
(2) Supports for tower
mounting
Cable locking system
Safety instructions
Quickstart guide

Phase (input)

1

Phase (output)

1

Internal bypass

Yes

Hot swap power

Yes

Resources

Brochures

[Eaton UPS and battery services - EN](#)

[Eaton UPS Services Quick Guide - EN](#)

Compliance information

[EU declaration of conformity Eaton 9PX UPS](#)

Declarations of conformity

[eaton-9px-declaration-of-conformity-en-us.pdf](#)

Manuals and user guides

[Eaton 9PX 1-3 kVA UPS and 9PX EBM 48V and 72V - Installation and user manual](#)

[Eaton Bypass Power Module \(BPM\) user guide](#)

[Eaton 9PX 1-3 kVA UPS - Quick Start Guide](#)

Specifications and datasheets

[Eaton Specification Sheet - 9PX2200IRTBPB](#)

Technical data sheets

[Eaton 9PX 1000-3000W UPS - Datasheet](#)

Auto shutdown function

Yes



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All rights reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia