



## PRODUCT INFORMATION SHEET

### UL Style 3340/3374

2ga 266X26T 3340/3374

125°C/150°C, 600 Vac, 750 Vdc, No flexing, Horizontal flame

#### Conductor

Size: 2 ga  
Number of Strands: 266  
Cross Section Area, Min: 32.95 mm<sup>2</sup>  
Conductor: Tinned Copper

#### Insulation

Insulation Material: 125°C/ 150°C No Flex EPDM  
Min Wall: 1.80 mm ( 0.071 in )  
Diameter, Reference Only: 11.71 mm ( 0.461 in )  
Separator: Physical

Voltage Rating: 600 Vac, 750 Vdc  
Temperature Rating: -40°C to 125°C/150°C No Flex EPDM  
Specifications: UL: 3340/3374  
CSA: CL-1254/AWM  
Part Number: 156175-81  
Packaging: Reels  
Print Legend: 2 AWG (UL LOGO) AWM STYLE 3340 OR 3374 125C/150C 600V PRESTOLITE P.G.  
CSA CL1254 OR AWM I A/B 125C 600V FT2  
Color: Black  
Other: RoHS Compliant